

**CB-HTR 140/3,5 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Our heat-stabilised cable ties made of polyamide 6.6 are suitable for continuous use at temperatures up to +125°C.

**General ordering data**

|            |   |
|------------|---|
| Version    | Cable ties, 3.5 x 140 mm, Polyamide 66, 180 N |
| Order No.  | <a href="#">2659380000</a>                    |
| Type       | CB-HTR 140/3,5 BK                             |
| GTIN (EAN) | 4050118682847                                 |
| Qty.       | 100 pc(s).                                    |

**CB-HTR 140/3,5 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Height     | 140 mm | Height (inches) | 5.512 inch |
| Width      | 3.5 mm | Width (inches)  | 0.138 inch |
| Net weight | 0.6 g  |                 |            |

**Temperatures**

|                                  |              |                                  |        |
|----------------------------------|--------------|----------------------------------|--------|
| Operating temperature range      | -40...125 °C | Continuous operating temp., min. | -40 °C |
| Continuous operating temp., max. | 125 °C       |                                  |        |

**Installation materials**

|                                   |        |                                   |              |
|-----------------------------------|--------|-----------------------------------|--------------|
| Bundle diameter, max.             | 32 mm  | Bundle diameter, min.             | 2.5 mm       |
| Cable diameter, max.              | 35 mm  | For re-opening                    | No           |
| Halogen                           | No     | Material                          | Polyamide 66 |
| Operating temperature range, max. | 125 °C | Operating temperature range, min. | -40 °C       |
| Tensile strength                  | 180 N  | Tensile strength (Pound-force)    | 40 lbf       |
| UL 94 flammability rating         | V-2    | UV-resistant                      | No           |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000046    | ETIM 7.0    | EC000046    |
| ETIM 8.0    | EC000046    | ETIM 9.0    | EC000046    |
| ECLASS 9.0  | 27-14-07-02 | ECLASS 9.1  | 27-14-07-02 |
| ECLASS 10.0 | 27-14-07-02 | ECLASS 11.0 | 27-14-07-02 |
| ECLASS 12.0 | 27-14-07-02 | ECLASS 13.0 | 27-14-07-02 |

**Approvals**

Approvals



ROHS

Conform

**Downloads**

Approval/Certificate/Document of Conformity

[EU Declaration of Conformity](#)

Catalogues

[Catalogues in PDF-format](#)

### CB-HTR 140/3,5 BK

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

