

VPCB PV I+II R 1000**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

'Abbildung ähnlich'

Versatile accessories round off the surge protection range. E.g. the all-purpose measuring device V-TEST, which is used to check the function of pluggable arresters such as VSPC.

General ordering data

Order No.	2665760000
Type	VPCB PV I+II R 1000
GTIN (EAN)	4050118686272
Qty.	20 pc(s).

VPCB PV I+II R 1000

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	52.2 mm	Depth (inches)	2.055 inch
Height	61.6 mm	Height (inches)	2.425 inch
Width	17.9 mm	Width (inches)	0.705 inch
Net weight	20 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 - 95% rel. humidity		

General data

Colour	grey	Design	miscellaneous
Protection degree	IP20	UL 94 flammability rating	V-0
Version	Miscellaneous		

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

Photovoltaic technical data

Conditions and requirements	EN 50539-11	Discharge current I_n (8/20 μ s)	20 kA
Discharge current, max. (8/20 μ s)	40 kA	Operating height in the grounded PV system	≤ 4000 m
PV system voltage, max. U_{cpv}	1,500 V	Requirements class	Type I/II
Short-circuit current I_{scpv}	11 kA		

Rated data IEC / EN

Discharge current, max. (8/20 μ s)	40 kA	Number of poles	1
Voltage type	DC		

Connection data

Type of connection	Solder connection, when screwed in
--------------------	------------------------------------

Guarantee

Time interval	5 years
---------------	---------

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

VPCB PV I+II R 1000

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data

[CAD data – STEP](#)

User Documentation

[Assembly instructions VPCB PV](#)

Catalogues

[Catalogues in PDF-format](#)


VPCB PV I+II R 1000

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings


Similar to illustration




Dimensioned drawing




Example of use



Electric symbol



Schematic circuit diagram



Application with arrestor

Socket type / Socket type / Type d'embase / Tipo di presa / Tipo de conector / 插座类型	Bezeichnung / Designation / Désignation / Designazione / 名称	Überstromschutz / Surge arrester / Parafoudre / Supratensore / 浪涌保护器	
Bestellnummer / Order number / Numéro de commande / Numero de pedido / 订单号	Bezeichnung / Designation / Désignation / Designazione / 名称	Bestellnummer / Order number / Numéro de commande / Numero de pedido / 订单号	
25430000	VPCB PV I+II R 1000	25060000	VPU PV I+II R 1000
25430001	VPCB PV I+II R 1000 T1	25060001	VPU PV I+II R 1000
25430002	VPCB PV I+II R 1000 T2	25060002	VPU PV I+II R 1000
25430003	VPCB PV I+II R 1000 T3	25060003	VPU PV I+II R 1000
25430004	VPCB PV I+II R 1000 T4	25060004	VPU PV I+II R 1000
25430005	VPCB PV I+II R 1000 T5	25060005	VPU PV I+II R 1000

1) R = Fernmeldeanlage / Remote signaling contacts / Contacts de télécommunication / Contatti di segnalazione remota / Contactos de señalización a distancia / 远端信号触点

Selection

VPCB PV I+II R 1000**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Spare Arrester****General ordering data**

Type	VPU PV I+II O 1000	Version
Order No.	2530600000	Surge voltage arrester, Low voltage, Accessories, Surge protection I /
GTIN (EAN)	4050118540819	II, Spare arrester
Qty.	9 pc(s).	