


SFX-VT 11/60 MM GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Highly flexible: SFX**

SFX markers are the preferred choice for labelling cables if you prefer the classic cable tie solution. Cables do not always run in a straight line. The material used in SFX markers addresses this fact with highly flexible polyurethane. The marker follows each curve of the cable and latches on with ease. Your advantages at a glance: Weathering resistance tested according to ISO DIN EN ISO 4892-2:2013 table 3, procedure A cycle 1 at 5000 hours

Individually labeled with the M-Print® PRO

Easy and fast printing with the THM MultiMark

General ordering data

Version	SlimFix, Conductor and cable markers, 7 - 40 mm, 60 x 13 mm, yellow
Order No.	2621440000
Type	SFX-VT 11/60 MM GE
GTIN (EAN)	4050118625608
Qty.	1,000 pc(s).
compatible printer	2599430000 2599440000

SFX-VT 11/60 MM GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	0.6 mm	Depth (inches)	0.024 inch
Height	60 mm	Height (inches)	2.362 inch
Width	13 mm	Width (inches)	0.512 inch
Net weight	0.55 g		

Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

General data

Colour	yellow	Halogen	No
Material	Polyolefine	Operating temperature range	-55...105 °C
Operating temperature range, max.	105 °C	Operating temperature range, min.	-55 °C
Printed characters	without	Size of labelling field	10.5 x 44 mm
Type of printing	neutral	UL 94 flammability rating	HB
Version	halogen-free	Width	13 mm

Conductor and cable markers

Cable tie passage	Flat	Conductor O.D.	7 - 40 mm
Conductor O.D., max.	40 mm	Conductor O.D., min.	7 mm
Conductor cross-section, max.	500 mm ²	Conductor cross-section, min.	16 mm ²
Cross-section for connected wire	16 - 500 mm ²	Halogen	No
Suitable cable tie	Plastic		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
White paper	Fact Sheet PV Markierer Fact Sheet EN PV Markers
Catalogues	Catalogues in PDF-format

SFX-VT 11/60 MM GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

