

WIL-LWXXXX-2700D024-450SXX0.3BM12GXXXX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The WIL-LED lights family: Only 8mm (9.4mm with magnet) high LED lamp for 24V DC with very high luminous efficacy and high lifespan (greater 60 000h). Very robust construction, by full potting and metal housing - water-proof (IP67). Due to its 2700K light color suitable for the various applications. Very easy to connect thanks to the M12 connection. Due to the low power consumption, a small enough power supply with 24V for operation.

General ordering data

Order No.	2633840000
Type	WIL-LWXXXX-2700D024-450SXX0.3BM12GXXXX
GTIN (EAN)	4050118648973
Qty.	1 pc(s).

WIL-LWXXXX-2700D024-450SXX0.3BM12GXXXX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	40 mm	Depth (inches)	1.575 inch
Height	8 mm	Height (inches)	0.315 inch
Width	450 mm	Width (inches)	17.716 inch
Net weight	442 g		

Temperatures

Operating temperature	-20 - 60°C
-----------------------	------------

Cable technical specifications

Cable Material	PUR	Sheathing colour	black
Cable length	0.3 m	Core cross-section	0.34 mm ²

Connection data

Version	pin, straight	Connection thread	M12
Coding	A-coded	Tightening torque	0.8 Nm
Wiring	Pin 4 (Strand: black) control white LED, Pin 3 (Strand: blue)		

Electric data

Rated voltage	24 V DC	Rated current	0.625 A
Power	15.0 W	Dimmable	Yes

General technical data

Electronic equipment on rolling stock	No	Recommended class according to UL for use of an power supply	NEC Class 2
Shape of the LED module	Rectangular	Type of connection	Pre-assembled cable
Number of LEDs	84	Light colour (CCT)	2700K, Warm white
Luminosity	525 cd	Light current	1,496 lm
Emitting angle	40 °	Illumination level	526 lux
Operating life	60.000 h	Type of mounting	Screw mounting
Drill hole spacing	435 mm	Impact resistance	IK05
Protection degree	IP67	Efficiency class (according to EU Directive No. 874/2012)	F

Material data

Housing main material	hard anodised aluminium	Encapsulation compound	PUR V0
Threaded ring material	PA	Material of end caps	Diecast zinc, nickel-plated

Classifications

ETIM 6.0	EC000996	ETIM 7.0	EC000996
ETIM 8.0	EC000996	ETIM 9.0	EC000996
ECLASS 9.1	27-11-06-35	ECLASS 10.0	27-11-06-35
ECLASS 11.0	27-11-06-35	ECLASS 12.0	27-11-06-35
ECLASS 13.0	27-11-06-35		

WIL-LWXXXX-2700D024-450SXX0.3BM12GXXXX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	bf1e8170-69bb-4440-b3e0-4da351a9a3b0
EPREL Registration number	1324734

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E354496


Downloads

Engineering Data	CAD data – STEP
User Documentation	Designation key WIL
Catalogues	Catalogues in PDF-format


Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

Drawings

Detailed drawing



Pole scheme



WIL-LWXXXX-2700D024-450SXX0.3BM12GXXXX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Motion sensor screw connection



Motion detector for the WIL-LED luminaire with screw connection. Switching time adjustable.

General ordering data

Type	WIL-BM-SK
Order No.	2537720000
GTIN (EAN)	4050118549157
Qty.	1 pc(s).

Motion sensor screw connection with cable



Motion detector for the WIL-LED luminaire with screw connection, 3m supply cable and M12 cable for connection to the WIL lamp. Switching time adjustable.

General ordering data

Type	WIL-BM-SK-M12-3.0U
Order No.	2537700000
GTIN (EAN)	4050118549140
Qty.	1 pc(s).

WIL-LWXXXX-2700D024-450SXX0.3BM12GXXXX**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Accessories****Magnet**

Magnet for WIL lights with 240mm total length, self-adhesive

Magnet**General ordering data**

Type	WIL-MAGNET
Order No.	2526810000
GTIN (EAN)	4050118537871
Qty.	1 pc(s).

Motion sensor Jackpac®

Motion detector for the WIL-LED luminaire with screw connection, 3m supply cable and M12 cable for connection to the WIL lamp. Switching time adjustable.

General ordering data

Type	WIL-BM-JP-M12-3.0U
Order No.	2537710000
GTIN (EAN)	4050118549164
Qty.	1 pc(s).

WIL-LWXXXX-2700D024-450SXX0.3BM12GXXXX**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Accessories****Swivelling holder**

Swivel bracket for WIL lights Very high quality version without detent

Swivelling holder**General ordering data**

Type	WIL-SCHWENKHALTER
Order No.	2614220000
GTIN (EAN)	4050118651249
Qty.	1 pc(s).

WIL power supply

Power supply IP65 for WIL standard family 85V-264V AC input, 24V DC output 400mA

Power Supply**General ordering data**

Type	WIL-NT-STANDARD
Order No.	2598350000
GTIN (EAN)	4050118611168
Qty.	1 pc(s).

WIL-LWXXXX-2700D024-450SXX0.3BM12GXXXX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Door switch



Door Switch

The WIL door switch is pre-assembled with an M12 cable and an access line. This allows for a simple Plug and Produce feature with our WIL LED lamp series.

General ordering data

Type	WIL-TS-M12
Order No.	2537730000
GTIN (EAN)	4050118549188
Qty.	1 pc(s).

Connect Power INSTA POWER



The single-phase INSTA-POWER switching power supplies are characterised by a wide power spectrum, compact design and good value for money. They are suitable for temperature ranges from -25°C to +70°C, have international approvals and a wide voltage input range. This makes them suitable for a wide range of applications. This also includes signal and telecommunications systems as well as automation systems with a low power requirement up to 96 Watt.

General ordering data

Type	PRO INSTA 30W 24V 1.3A	Version
Order No.	2580190000	Power supply, switch-mode power supply unit, 24 V
GTIN (EAN)	4050118590920	
Qty.	1 pc(s).	

WIL-LWXXXX-2700D024-450SXX0.3BM12GXXXX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****PUR halogen-free black (U)**

Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

The M8 and M12 sensor-actuator cables are supplied as standard with brass nickel-plated nuts. However if you are looking to use our products in an extremely harsh environment, we can also supply a variant with a plastic nut. This enables use in environments where cables with nickel-plated M8 and M12 nuts would rust.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

Type	SAIP-M12BG-3-3.0U	Version
Order No.	1108730300	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4032248888481	poles : 3, 3 m, Female socket, straight, Shielded: No, LED: No, Sheath
Qty.	1 pc(s).	material: PUR, Halogen: No

PUR halogen-free black (U)

Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

Type	SAIL-M12BG-3-3.0U	Version
Order No.	9457820300	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4032248228195	poles : 3, 3 m, Female socket, straight, Shielded: No, LED: No, Sheath
Qty.	1 pc(s).	material: PUR, Halogen: No

WIL-LWXXXX-2700D024-450SXX0.3BM12GXXXX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Straight**

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

General ordering data

Type	SAIB-4/7	Version
Order No.	9457240000	Field attachable connector, M12, Female socket, straight
GTIN (EAN)	4008190312275	
Qty.	1 pc(s).	
Type	SAIS-4/7	Version
Order No.	9457550000	Field attachable connector, M12, pin, straight
GTIN (EAN)	4032248167647	
Qty.	1 pc(s).	

WIL-LWXXXX-2700D024-450SXX0.3BM12GXXXX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

