

**IE-SW-EL10-8GTPOE-2GESFP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Features of EcoLine Power-over-Ethernet unmanaged switches/injectors**

- Variants with 2, 4 or 8 IEEE 802.3af/at compliant PoE ports (up to 30 watt power output per PoE port)
- Integrated DC/DC converter for providing PoE voltage to PDs over the entire PSE input voltage range from 12 to 57 V DC
- Models supporting Gigabit Ethernet including Jumbo Frame support for applications with high demand on bandwidth and latency
- Models with fiber optic ports for communication links over long distances
- Suitable for use in harsh industrial environment thanks to rugged design and wide operating temperature range of -40°C up to 75°C
- Reliable operation due to redundant voltage inputs, fault relay and LED diagnostics

**General ordering data**

Version	Network switch, unmanaged PoE, Gigabit Ethernet, Number of ports: 8x RJ45 10/100/1000 BaseT(X) PoE+, 2x 100/1000BaseSFP Slot, IP30, -40 °C...75 °C
Order No.	<a href="#">2682410000</a>
Type	IE-SW-EL10-8GTPOE-2GESFP
GTIN (EAN)	4050118692303
Qty.	1 pc(s).

## IE-SW-EL10-8GTPOE-2GESFP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	108.3 mm	Depth (inches)	4.264 inch
Height	145.1 mm	Height (inches)	5.713 inch
Width	54.3 mm	Width (inches)	2.138 inch
Net weight	969 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...75 °C
Humidity	5 to 95 % (non-condensing)		

## EMC conformity and approvals

EMC standards	EN 55032, EN 55024, CISPR 32, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 4 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz bis 1 GHz: 3 V/m, IEC 61000-4-4 EFT: Power: 0.5 kV; Signal: 0.5 kV, IEC 61000-4-5 Surge: Power: 0.5 kV; Signal: 1 kV, IEC 61000-4-6 CS: 3 Vrms	Free fall	
Safety standard	UL 61010-1, UL 61010-2-201	Shock	According to IEC 60068-2-31 according to IEC 60068-2-27
Vibration	according to IEC 60068-2-6		

## Environmental conditions

Humidity	5 to 95 % (non-condensing)		
Operating altitude	Altitude, max.	2,000 m	
	Note	in acc. with UL	
	Altitude, max.	6,000 m	
	Note	for restrictions, see the manufacturer's declaration for operating altitude in section downloads	
Operating temperature, max.	75 °C		
Operating temperature, min.	-40 °C		
Storage temperature, max.	85 °C		
Storage temperature, min.	-40 °C		

## Guarantee

Time interval	5 years
---------------	---------

**IE-SW-EL10-8GTPOE-2GESFP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Interfaces**

Fibre-optic ports		Function DIP switch	2x for enabling/disabling power fault alarm via relay, 2x for switching between 100BaseSFP and 1000BaseSFP on SFP port
	100/1000Base SFP Slot		
LED indicator	Power LED: PWR1, PWR2, FAULT, Port LED: LNK/ACT, PoE active	Number of ports	8x RJ45 10/100/1000 BaseT(X) PoE+, 2x 100/1000BaseSFP Slot
RJ45 ports	10/100/1000BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port	Signalling contact	1 relay output with a current capacity of 1 A at 24 V DC

**MTBF**

MTBF	According to Standard	Telcordia SR-332
	Operating time (hours), min.	537,330 h

**Power over Ethernet (PoE)**

PoE output current	Standard	IEEE 802.3af
	Output current	350 mA
	Standard	IEEE 802.3at
	Output current	600 mA
PoE output power	Standard	IEEE 802.3af
	Output power	15.4 W
	Standard	IEEE 802.3at
	Output power	30 W
PoE pin assignment	Mode A: Pin 1, 2 (V+); Pin 3, 6 (V-); Alternative A: MDI	
Total PoE power budget	Voltage type	DC
	Voltage, min.	12 V
	Voltage, max.	23.9 V
	Power budget	60 W
	Voltage type	DC
	Voltage, min.	24 V
	Voltage, max.	57 V
	Power budget	120 W

**Power supply**

Connection type	1 removable 6-pin terminal block	
Current consumption	Voltage	12 V
	Current	7.12 A
	Voltage	24 V
	Current	6.13 A
	Voltage	48 V
	Current	2.95 A
Overload current protection	Yes	
Reverse polarity protection	Yes	
Voltage supply	12/24/48 V DC, 2 redundant inputs	
Voltage supply range	Voltage type	DC
	Voltage, min.	12 V
	Voltage, max.	57 V

## IE-SW-EL10-8GTPOE-2GESFP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Switch characteristics

Bandwidth backplane	20 Gbit/s	Jumbo frame support	up to 9.6 KB
MAC table size	8 K	Packet buffer size	4 Mbit

## Technical data

Housing main material	Metal	Protection degree	IP30
Speed	Gigabit Ethernet	Switch	unmanaged PoE
Type of mounting	DIN rail		

## Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control
Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X) and 100BaseFX, IEEE 802.3ab for 1000Base-T, IEEE 802.3z for 1000BaseX, IEEE 802.3x for flow control, IEEE 802.3at/af for Power-over-Ethernet		

## Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
ETIM 8.0	EC000734	ETIM 9.0	EC000734
ECLASS 9.0	19-17-01-06	ECLASS 9.1	19-17-01-06
ECLASS 10.0	19-17-04-10	ECLASS 11.0	19-17-04-10
ECLASS 12.0	19-17-04-10	ECLASS 13.0	19-17-04-10

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9229992a-00b9-4096-8962-200a7f33e289

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity</a> <a href="#">RCM Declaration of Conformity</a> <a href="#">UK Declaration of Conformity</a> <a href="#">Manufacturer's declaration for operating altitude</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Hardware Installation Guide</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

Creation date May 4, 2024 7:30:36 PM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.