

**IE-SW-EL05-4GT-1GESFP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Features of EcoLine unmanaged Switch series**

- Huge variety of port count and media type enable a wide range of applications (5 to 24 ports)
- Models supporting Gigabit Ethernet including Jumbo Frame support for applications with high demand on bandwidth and latency
- Suitable for use in harsh industrial environment thanks to rugged design and wide operating temperature range of -40°C up to 75°C
- Reliable operation due to redundant voltage inputs, fault relay and LED diagnostics

**General ordering data**

Version	Network switch, unmanaged, Gigabit Ethernet, Number of ports: 4 x RJ45, 1x 1000BaseSFP Slot, IP30, -40 °C...75 °C
Order No.	<a href="#">2682220000</a>
Type	IE-SW-EL05-4GT-1GESFP
GTIN (EAN)	4050118692495
Qty.	1 pc(s).

**IE-SW-EL05-4GT-1GESFP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	94.9 mm	Depth (inches)	3.736 inch
Height	144.3 mm	Height (inches)	5.681 inch
Width	26.1 mm	Width (inches)	1.028 inch
Net weight	420 g		

**Temperatures**

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...75 °C
Humidity	5 to 95 % (non-condensing)		

**EMC conformity and approvals**

EMC standards	EN 55032, EN 55024, CISPR 32, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 4 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz bis 1 GHz: 3 V/m, IEC 61000-4-4 EFT: Power: 0.5 kV; Signal: 0.5 kV, IEC 61000-4-5 Surge: Power: 0.5 kV; Signal: 1 kV, IEC 61000-4-6 CS: 3 Vrms	Free fall	
Safety standard	UL 61010-1, UL 61010-2-201	Shock	According to IEC 60068-2-31 according to IEC 60068-2-27
Vibration	according to IEC 60068-2-6		

**Environmental conditions**

Humidity	5 to 95 % (non-condensing)		
Operating altitude	Altitude, max.	2,000 m	
	Note	in acc. with UL	
	Altitude, max.	6,000 m	
	Note	for restrictions, see the manufacturer's declaration for operating altitude in section downloads	
Operating temperature, max.	75 °C		
Operating temperature, min.	-40 °C		
Storage temperature, max.	85 °C		
Storage temperature, min.	-40 °C		

**Guarantee**

Time interval	5 years
---------------	---------

## IE-SW-EL05-4GT-1GESFP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Interfaces

Fibre-optic ports	1000BaseSFP-Slot	Function DIP switch	2x for enabling/disabling power fault alarm via relay
LED indicator	Power LED: PWR1, PWR2, FAULT, Port LED: LNK/ACT, 10/100/1000M (RJ45 port), LNK/ACT (SFP port)	Number of ports	4 x RJ45, 1x 1000BaseSFP Slot
RJ45 ports	10/100/1000BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port	Signalling contact	1 relay output with a current capacity of 1 A at 24 V DC

## MTBF

MTBF	According to Standard	Telcordia SR-332
	Operating time (hours), min.	1,861,840 h

## Power supply

Connection type	1 removable 6-pin terminal block	
Current consumption	Voltage	24 V
	Current	0.18 A
Overload current protection	Yes	
Reverse polarity protection	Yes	
Voltage supply	12/24/48 V DC, 2 redundant inputs	
Voltage supply range	Voltage type	DC
	Voltage, min.	10.8 V
	Voltage, max.	52.8 V

## Switch characteristics

Bandwidth backplane	10 Gbit/s	Jumbo frame support	up to 10 KB
MAC table size	1 K	Packet buffer size	1 Mbit

## Technical data

Housing main material	Metal	Protection degree	IP30
Speed	Gigabit Ethernet	Switch	unmanaged
Type of mounting	DIN rail		

## Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control
Standard	IEEE 802.3 for 10BASE-T, IEEE 802.3u for 100BASE-TX, IEEE 802.3ab for 1000BASE-T, IEEE 802.3z for 1000BASE-X, IEEE 802.3x for flow control		

## IE-SW-EL05-4GT-1GESFP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
ETIM 8.0	EC000734	ETIM 9.0	EC000734
ECLASS 9.0	19-17-01-06	ECLASS 9.1	19-17-01-06
ECLASS 10.0	19-17-04-02	ECLASS 11.0	19-17-04-02
ECLASS 12.0	19-17-04-02	ECLASS 13.0	19-17-04-02

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9229992a-00b9-4096-8962-200a7f33e289

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity</a> <a href="#">RCM Declaration of Conformity</a> <a href="#">UK Declaration of Conformity</a> <a href="#">Manufacturer's declaration for operating altitude</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Hardware Installation Guide</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## IE-SW-EL05-4GT-1GESFP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## SFP transceiver (for use with switches of Eco- Advanced- and SubstationLine)



## Features of SFP-Transceiver series

- Huge variety of transceiver types for several transmission speeds (up to 10 Gigabit Ethernet) and distances (up to 60 km)
- BiDi SFP models for communication via single fiber
- Easy control of transceiver status due to support of Digital Diagnostic Monitoring (DDM)
- Hot pluggable (during operation)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Eco-, Advanced- and SubstationLine

## General ordering data

Type	IE-SFP-1GE-SM-10-BIDI-T ...	Version
Order No.	<a href="#">2682530000</a>	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 10 km,
GTIN (EAN)	4050118692181	-40 °C...85 °C
Qty.	1 pc(s).	
Type	IE-SFP-1GE-SM-20-BIDI-T ...	Version
Order No.	<a href="#">2682540000</a>	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 20 km,
GTIN (EAN)	4050118692174	-40 °C...85 °C
Qty.	1 pc(s).	
Type	IE-SFP-1GE-SM-10	Version
Order No.	<a href="#">2682500000</a>	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 10 km, -40
GTIN (EAN)	4050118692211	°C...85 °C
Qty.	1 pc(s).	
Type	IE-SFP-1GE-SM-40	Version
Order No.	<a href="#">2682510000</a>	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 40 km, -40
GTIN (EAN)	4050118692204	°C...85 °C
Qty.	1 pc(s).	
Type	IE-SFP-1GE-MM-05	Version
Order No.	<a href="#">2682480000</a>	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 0.5 km, -40
GTIN (EAN)	4050118692235	°C...85 °C
Qty.	1 pc(s).	
Type	IE-SFP-1GE-MM-2	Version
Order No.	<a href="#">2682490000</a>	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 2 km, -40 °C...85
GTIN (EAN)	4050118692228	°C
Qty.	1 pc(s).	
Type	IE-SFP-1GE-SM-10-BIDI-T ...	Version
Order No.	<a href="#">2682520000</a>	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 10 km,
GTIN (EAN)	4050118692198	-40 °C...85 °C
Qty.	1 pc(s).	
Type	IE-SFP-1GE-SM-20-BIDI-T ...	Version
Order No.	<a href="#">2682550000</a>	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 20 km,
GTIN (EAN)	4050118692167	-40 °C...85 °C
Qty.	1 pc(s).	

**IE-SW-EL05-4GT-1GESFP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Mounting kit for 19" rack assembly**

- For assembling DIN rail-based devices on 19" racks

**General ordering data**

Type	RM-KIT	Version
Order No.	<a href="#">1241440000</a>	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 pc(s).	