

**IE-SW-AL08M-8TX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Features of AdvancedLine managed Switch series**

Industrial networks require a future-proof infrastructure with high availability, reliability, and transparency. Managed switches increase network availability utilizing redundancies and control mechanisms as well as network diagnostics in demanding automation networks.

- Extensive set of management features enable the set-up of various redundancy, monitoring, traffic filter and security functions
- Huge variety of port count and media type enable a wide range of applications (5 to 24 ports)
- Models supporting Gigabit Ethernet including Jumbo Frame support for applications with high demand on bandwidth and latency
- Suitable for use in harsh industrial environment thanks to rugged design and wide operating temperature range of -40°C up to 75°C

**General ordering data**

Version	Network switch, managed, Fast Ethernet, Number of ports: 8x RJ45, IP30, -40 °C...75 °C
Order No.	<a href="#">2682280000</a>
Type	IE-SW-AL08M-8TX
GTIN (EAN)	4050118692433
Qty.	1 pc(s).

## IE-SW-AL08M-8TX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	107.1 mm	Depth (inches)	4.217 inch
Height	144.3 mm	Height (inches)	5.681 inch
Width	52 mm	Width (inches)	2.047 inch
Net weight	812 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...75 °C
Humidity	5 to 95 % (non-condensing)		

## EMC conformity and approvals

EMC standards	EN 55032, EN 55024, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 4 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz bis 1 GHz: 3 V/m, IEC 61000-4-4 EFT: Power: 0.5 kV; Signal: 0.5 kV, IEC 61000-4-5 Surge: Power: 0.5 kV; Signal: 1 kV, IEC 61000-4-6 CS: 3 Vrms	Free fall	
Safety standard	SELV according to EN 62368-1, UL 61010-1, UL 61010-2-201	Shock	According to IEC 60068-2-31 according to IEC 60068-2-27
Vibration	according to IEC 60068-2-6		

## Environmental conditions

Humidity	5 to 95 % (non-condensing)		
Operating altitude	Altitude, max.	2,000 m	
	Note	in acc. with UL	
	Altitude, max.	6,000 m	
	Note	for restrictions, see the manufacturer's declaration for operating altitude in section downloads	
Operating temperature, max.	75 °C		
Operating temperature, min.	-40 °C		
Storage temperature, max.	85 °C		
Storage temperature, min.	-40 °C		

## Guarantee

Time interval	5 years
---------------	---------

## Interfaces

Alarm contact	1 relay output with a current capacity of 1 A at 24 V DC	Console port interface	RS-232 (RJ45 connector)
Function reset button	<5 sec: System reboot, >5 sec: Factory default	Number of ports	8x RJ45
RJ45 ports	10/100BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port		

Creation date May 4, 2024 8:51:24 AM CEST

## IE-SW-AL08M-8TX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## MTBF

MTBF	According to Standard	Telcordia SR-332
	Operating time (hours), min.	841,599 h

## Management features

Device configuration	Webbrowser (HTTP/HTTPS), SNMP v1/v2c/v3, Local serial console port (RS-232 via RJ-45 port), Upload of a configuration file via web-interface or TFTP-Server, Command Line Interface (Telnet/SSH)	Monitoring function	SNMP v1/v2c/v3, Link Layer Discovery Protocol (LLDP), Port mirroring, Port statistics, Port monitoring, Syslog, RMON (Remote monitoring), Event based warning via E-Mail, Event based warning via relay, Event based warning via SNMP trap
Network redundancy	Spanning Tree Protocol (STP), Rapid Spanning Tree Protocol (RSTP), Multiple Spanning Tree Protocol (MSTP), O-Ring (recovery time <10 ms), O-Chain (recovery time <10 ms), Link Aggregation Control Protocol (LACP), Fast recovery	Network traffic filter	Quality of Service (QoS), Class of Service (CoS), Type of Service (ToS), Differentiated Services Code Point (DSCP), Port based VLAN, Tag based VLAN, GVRP (GARP VLAN Registration Protocol), IGMP v2/v3, Multicast VLAN Registration (MVR), Traffic Rate Limiting
IP-address management	Static, DHCP-Client, DHCP-Server (port based, pool-based), DHCP Option 82, DHCP-Relay	Security functions	VLAN segmentation, Enable/disable ports, TACACS+ and IEEE 802.1X User Authentication, Access control (port based via IEEE 802.1X), Access control list (IP-based), Access control list (MAC-based), Management access security via secure IP-list and configuration of allowed access methods (web-interface, telnet, SSH), Loop protection
Time synchronization management	NTP server, SNTP client	Industrial protocol support	Modbus/TCP slave, PROFINET device acc. to conformance class A

## Power supply

Connection type	1 removable 7-pin terminal block	
Current consumption	Voltage	12 V
	Current	0.47 A
	Voltage	24 V
	Current	0.24 A
	Voltage	48 V
	Current	0.12 A
Overload current protection	Yes	
Reverse polarity protection	Yes	
Voltage supply	12/24/48 V DC, 2 redundant inputs	
Voltage supply range	Voltage type	DC
	Voltage, min.	10.8 V
	Voltage, max.	52.8 V

Creation date May 4, 2024 8:51:24 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

## IE-SW-AL08M-8TX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Switch characteristics

Bandwidth backplane	1.6 Gbit/s	IGMP-Groups	1,024
MAC table size	8 K	Max. number of available VLANs	4,095
Packet buffer size	1 Mbit	Priority queues	4
VLAN-ID max	4,094	VLAN-ID min	1

## Technical data

Housing main material	Metal	Protection degree	IP30
Speed	Fast Ethernet	Switch	managed
Type of mounting	DIN rail		

## Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control
Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X), IEEE 802.3x for flow control, IEEE 802.3ad for port trunk with LACP, IEEE 802.1D for the Spanning Tree protocol, IEEE 802.1w for Rapid STP, IEEE 802.1s for the Multiple Spanning Tree Protocol (MSTP), IEEE 802.1p for Class of Service, IEEE 802.1Q for VLAN tagging, IEEE 802.1X for authentication, IEEE 802.1AB for Link Layer Discovery protocol (LLDP)		

## Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
ETIM 8.0	EC000734	ETIM 9.0	EC000734
ECLASS 9.0	19-17-01-06	ECLASS 9.1	19-17-01-06
ECLASS 10.0	19-17-04-01	ECLASS 11.0	19-17-04-01
ECLASS 12.0	19-17-04-01	ECLASS 13.0	19-17-04-01

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9229992a-00b9-4096-8962-200a7f33e289

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Creation date May 4, 2024 8:51:24 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

## IE-SW-AL08M-8TX

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">KC certificate</a>
	<a href="#">EU Declaration of Conformity</a>
	<a href="#">RCM Declaration of Conformity</a>
	<a href="#">UK Declaration of Conformity</a>
	<a href="#">Manufacturer's declaration for operating altitude</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Product Change Notification	<a href="#">Firmware Release Notes</a>
Software	<a href="#">Device description – SNMP private MIB</a>
	<a href="#">Firmware – Current Firmware</a>
User Documentation	<a href="#">Hardware Installation Guide</a>
	<a href="#">User manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>