

**IE-SFP-1GE-SM-20-BIDI-TX1550****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Features of SFP-Transceiver series**

- Huge variety of transceiver types for several transmission speeds (up to 10 Gigabit Ethernet) and distances (up to 60 km)
- BiDi SFP models for communication via single fiber
- Easy control of transceiver status due to support of Digital Diagnostic Monitoring (DDM)
- Hot pluggable (during operation)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Eco-, Advanced- and SubstationLine

**General ordering data**

Version	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 20 km, -40 °C...85 °C
Order No.	<a href="#">2682550000</a>
Type	IE-SFP-1GE-SM-20-BIDI-TX1550
GTIN (EAN)	4050118692167
Qty.	1 pc(s).

**IE-SFP-1GE-SM-20-BIDI-TX1550****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	17.5 g
------------	--------

**Temperatures**

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 to 95 % (non-condensing)		

**EMC conformity and approvals**

EMC standards	EN 55032, EN 55035	Safety standard	UL 62368-1
---------------	--------------------	-----------------	------------

**Environmental conditions**

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	85 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

**Fibre optic transceiver characteristics**

Transmission rate	1000 Mbps	
Digital diagnostic monitor function (DDM)	Supported	
Transceiver type	Singlemode BiDi	
Connector type	LC-Simplex	
Transmission distance, typ.	20 km	
Wavelength	Wavelength	TX
	typ.	1,550 nm
	Wavelength	RX
	typ.	1,310 nm
	Wavelength	TX
	min.	1,510 nm
	max.	1,570 nm
	Wavelength	RX
	min.	1,250 nm
	max.	1,380 nm
Receive power	min.	-23 dBm
	max.	-3 dBm
Transmission power	min.	-8 dBm
	max.	-2 dBm
Link-budget	15 dB	
Note	BiDi-SFP transceivers must be used in pairs (e.g. IE-SFP-1GE-SM-10-BIDI-TX1310 and IE-SFP-1GE-SM-10-BIDI-TX1550 or IE-SFP-1GE-SM-20-BIDI-TX1310 and IE-SFP-1GE-SM-20-BIDI-TX1550).	
Note	When connecting a single-mode fiber transceiver over a short distance, we recommend using an attenuator to prevent the transceiver from being damaged by excessive optical power.	

**Guarantee**

Time interval	3 years
---------------	---------

**Power supply**

Voltage supply	3.3 V (via Ethernet switch)
----------------	-----------------------------

Creation date May 22, 2024 2:02:17 AM CEST

**IE-SFP-1GE-SM-20-BIDI-TX1550****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Technical data**

Type of mounting	Insert in SFP slot
------------------	--------------------

**Classifications**

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC003628	ETIM 9.0	EC003628
ECLASS 9.1	27-44-02-92	ECLASS 10.0	27-44-02-92
ECLASS 11.0	19-17-03-03	ECLASS 12.0	19-17-03-03
ECLASS 13.0	19-17-03-03		

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E230683

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity</a> <a href="#">RCM Declaration of Conformity</a> <a href="#">UK Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>