


**FBCON PA CG 6WAY LIMITER R-TS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

For standard industrial applications (non-hazardous areas), PROFIBUS PA junction boxes and limiters are available as 1-way, 2-way, 4-way, and 8-way distributors. FBCon limiters are designed to protect connected field devices from over voltages and short circuits. As voltage-limiting protective elements, suppressor diodes are used. Due to the integrated current limitation, the segment is also protected against short circuit on a spur line. EMC cable glands, protection class IP66 and a wide operating temperature range safely protect your connections in harsh environments.

**Functionality**

- EMC cable glands for trunk and spurs
- M12 connector for spurs
- External earthing stud
- Pressure equalizing element
- Protection class IP66
- Aluminium and stainless-steel versions
- Profibus PA / Foundation Fieldbus compatible

Note: The use of FBCon products with aluminum enclosures and / or M12 connectors is not recommended in strongly saline environments.

**General ordering data**

Version	Standard distributor with current limiting, 6-channel distributor LIMITER, IP66, IP67, Trunk line M20
Order No.	<a href="#">2703870000</a>
Type	FBCON PA CG 6WAY LIMITER R-TS
GTIN (EAN)	4064675266662
Qty.	1 pc(s).

## FBCON PA CG 6WAY LIMITER R-TS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	34 mm	Height (inches)	1.339 inch
Width	175 mm	Width (inches)	6.89 inch
Length	80 mm	Length (inches)	3.15 inch
Net weight	660 g		

## Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...75 °C
---------------------	----------------	-----------------------	----------------

## Technical data

Bus system	Profibus-PA, Foundation Fieldbus	Cable entry	Trunk line M20
Cable glands	Brass cable gland	Current limiting	adjustable, 20 mA, 40 mA, 60 mA
Design of housing	With pressure compensation element	Housing main material	Aluminium, Aluminum
Housing surface	polished	Operating voltage $U_{max}$ , max.	32 V
Pollution severity	3	Protection degree	IP66, IP67
Type of distribution	6-channel distributor LIMITER	Type of mounting	surface-mounted

## Classifications

ETIM 6.0	EC001604	ETIM 7.0	EC001604
ETIM 8.0	EC001604	ETIM 9.0	EC001604
ECLASS 9.0	27-24-26-08	ECLASS 9.1	27-24-26-08
ECLASS 10.0	27-24-26-08	ECLASS 11.0	27-24-26-08
ECLASS 12.0	27-44-01-11	ECLASS 13.0	27-44-01-11

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	3a5f5913-76fc-4ff5-8563-4463f80bbe02

## Approvals

Approvals



UL File Number Search	UL Website
Certificate no. (cULus)	E141197

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Software	<a href="#">Runtime Software – WI-Segment-Calculator</a>
User Documentation	<a href="#">Quick start guide – Application-Guide-Planning and installing Fieldbus networks-using-FBCon_english_deutsch</a> <a href="#">Device description – FBCon Segment Calculator_english</a> <a href="#">Instruction sheet</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## FBCON PA CG 6WAY LIMITER R-TS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

