

CH-HFAB-XXXX-06-0500-AH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product similar to the picture



The increasingly networked industrial world goes hand in hand with the modularization of machines and systems. Functions from the control cabinet are increasingly being moved to field level, which drives up the amount of cabling required.

Our ready-for-connection cable assemblies can be used wiring in field level and for transmitting data or power in various applications. The Plug & Produce solution by Weidmüller are fully tested and will lead to simplification of assembly on your machine. This allows you to focus on your core competencies and further increase your efficiency.

With our broad product portfolio of certified components, we offer you a wide diversification so that we can provide you the perfect solution for your application.

If you cannot find the cable assembly you are looking for despite our continuously growing portfolio, we can also offer you different length variants and customer-specific solutions.

General ordering data

Version	Heavy duty connector assemblies, Socket connector, Lapp ÖLFLEX® CLASSIC 110 BK 7G1.5 or similar, Shielded: No, Number of poles: 6
Order No.	2712260500
Type	CH-HFAB-XXXX-06-0500-AH
GTIN (EAN)	4050118751178
Qty.	1 pc(s).

CH-HFAB-XXXX-06-0500-AH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	1,748.527 g
------------	-------------

Temperatures

Limit temperature	-40 °C ... 80 °C
-------------------	------------------

Technical specifications for cable

Bending radius, min., moving	10 x cable diameter	Bending radius, min., stationary	4 x cable diameter
Cable length	5	Core cross-section	1.5 mm ²
Halogen	Yes	Insulation	PVC
Number of poles	6	Number of wires	7
Outside diameter	8.9 mm	Sheath material	PVC
Sheathing colour	black	Shielded	No
Temperature range, moving	-15...70 °C	Temperature range, stationary	-40...80 °C

General technical data

Protection degree	IP65	Rated voltage	500 V
Version	Socket connector		

General Technical Data

Number of poles	6	Pin arrangement	1:1, numbered cores
Protection degree	IP65	Rated voltage	500 V

Technical Specifications Connector

Connector	Cable entry	angled
	Housing main material	Diecast aluminium
	Series	HE
	Size	3
	Type	Female
	Individual components connector	HDC 06B TSLU 1M20G HDC HE 6 FP H1.5/14 R VG M20 - MS 68

Technical specifications for cable

Bending radius, min., moving	10 x cable diameter	Bending radius, min., stationary	4 x cable diameter
Cable length	5	Core cross-section	1.5 mm ²
Halogen	Yes	Insulation	PVC
Line type	Lapp ÖLFLEX® CLASSIC 110 BK 7G1.5 or similar	Number of wires	7
Outside diameter	8.9 mm	Sheath material	PVC
Sheathing colour	black	Shielded	No
Temperature range, moving	-15...70 °C	Temperature range, moving, max.	70 °C
Temperature range, moving, min.	-15 °C	Temperature range, stationary	-40...80 °C
Temperature range, stationary, max.	80 °C	Temperature range, stationary, min.	-40 °C

CH-HFAB-XXXX-06-0500-AH**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC001576	ETIM 7.0	EC001576
ETIM 8.0	EC001576	ETIM 9.0	EC001576
ECLASS 9.0	27-06-04-02	ECLASS 9.1	27-06-91-90
ECLASS 10.0	27-06-04-02	ECLASS 11.0	27-06-04-02
ECLASS 12.0	27-06-04-02	ECLASS 13.0	27-06-04-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	81ca46c4-2930-4739-aa54-e07d33c98f2c

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

CH-HFAB-XXXX-06-0500-AH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Bulkhead housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 06B ADLU	Version
Order No.	1202500000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Bulkhead housing, End-locking clamp, lower side, End-locking clamp not replaceable, Standard, with cover
GTIN (EAN)	4008190889920	
Qty.	1 pc(s).	
Type	HDC 06B ALU	Version
Order No.	1202100000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Bulkhead housing, End-locking clamp, lower side, End-locking clamp not replaceable, Standard
GTIN (EAN)	4008190149369	
Qty.	1 pc(s).	
Type	HDC 06B ALU N	Version
Order No.	2488560000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Bulkhead housing, End-locking clamp, lower side, Standard, without cover
GTIN (EAN)	4050118541502	
Qty.	1 pc(s).	
Type	HDC 06B ADLU N	Version
Order No.	2559320000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Bulkhead housing, End-locking clamp, lower side, Standard
GTIN (EAN)	4050118652345	
Qty.	1 pc(s).	
Type	HDC 06B ALU O-RING	Version
Order No.	1019870000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Bulkhead housing, End-locking clamp, lower side, End-locking clamp not replaceable, Standard
GTIN (EAN)	4032248731985	
Qty.	1 pc(s).	

CH-HFAB-XXXX-06-0500-AH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Coupling hood



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 16D KLU 1PG21G	Version
Order No.	1653230000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Coupling housing, End-locking clamp, lower side, high, Size of cable entries: PG 21
GTIN (EAN)	4008190403300	
Qty.	1 pc(s).	
Type	HDC 06B KLU 1M25G	Version
Order No.	1021330000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Coupling housing, End-locking clamp, lower side, Standard, Size of cable entries: PG 16
GTIN (EAN)	4032248734948	
Qty.	1 pc(s).	
Type	HDC 06B KLU 1PG16G	Version
Order No.	1653200000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Coupling housing, End-locking clamp, lower side, Standard, Size of cable entries: PG 16
GTIN (EAN)	4008190403270	
Qty.	1 pc(s).	

CH-HFAB-XXXX-06-0500-AH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Cover



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 06B DMDL 1LB	Version
Order No.	1665210000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Cover for upper part of housing, End-locking clamp, lower side, Standard
GTIN (EAN)	4008190421915	
Qty.	1 pc(s).	

Base housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 16D SDLU 1M25G	Version
Order No.	1900820000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, high, with cover, Size of cable entries: M 25
GTIN (EAN)	4032248521098	
Qty.	1 pc(s).	
Type	HDC 06B SDLU 2PG16G	Version
Order No.	1652990000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, Standard, with cover, Size of cable entries: PG 16
GTIN (EAN)	4008190403065	
Qty.	1 pc(s).	

CH-HFAB-XXXX-06-0500-AH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	HDC 16D SLU 1M25G	Version
Order No.	1900880000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, high, without cover, Size of cable entries: M 25
GTIN (EAN)	4032248521111	
Qty.	1 pc(s).	
Type	HDC 06B SDLU 1M25G	Version
Order No.	1900380000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, Standard, with cover, Size of cable entries: M 25
GTIN (EAN)	4032248592913	
Qty.	1 pc(s).	
Type	HDC 06B SDLU 2M20G	Version
Order No.	1788170000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, Standard, with cover, Size of cable entries: M 20
GTIN (EAN)	4032248205608	
Qty.	1 pc(s).	
Type	HDC 06B SLU 1M20G	Version
Order No.	1900460000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, Standard, without cover, Size of cable entries: M 20
GTIN (EAN)	4032248585939	
Qty.	1 pc(s).	
Type	HDC 06B SLU 2M25G	Version
Order No.	1788130000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, Standard, without cover, Size of cable entries: M 25
GTIN (EAN)	4032248205578	
Qty.	1 pc(s).	
Type	HDC 16D SLU 2M25G	Version
Order No.	1787520000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, high, without cover, Size of cable entries: M 25
GTIN (EAN)	4032248204861	
Qty.	1 pc(s).	
Type	HDC 16D SLU 2M32G	Version
Order No.	1787510000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, high, without cover, Size of cable entries: M 32
GTIN (EAN)	4032248204854	
Qty.	1 pc(s).	
Type	HDC 06B SDLU 2M25G	Version
Order No.	1788160000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, Standard, with cover, Size of cable entries: M 25
GTIN (EAN)	4032248205592	
Qty.	1 pc(s).	
Type	HDC 06B SLU 1PG16G	Version
Order No.	1652750000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, Standard, without cover, Size of cable entries: PG 16
GTIN (EAN)	4008190402822	
Qty.	1 pc(s).	
Type	HDC 06B SDLU 1M20G	Version
Order No.	1900360000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, Standard, with cover, Size of cable entries: M 20
GTIN (EAN)	4032248585922	
Qty.	1 pc(s).	
Type	HDC 16D SDLU 2M25G	Version
Order No.	1787540000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, high, with cover, Size of cable entries: M 25
GTIN (EAN)	4032248204885	
Qty.	1 pc(s).	
Type	HDC 06B SLU 2M20G	Version
Order No.	1788140000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, Standard, without cover, Size of cable entries: M 20
GTIN (EAN)	4032248205585	
Qty.	1 pc(s).	
Type	HDC 06B SLU 1M25G	Version
Order No.	1900480000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, Standard, without cover, Size of cable entries: M 25
GTIN (EAN)	4032248585946	
Qty.	1 pc(s).	

Creation date May 2, 2024 12:29:48 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

CH-HFAB-XXXX-06-0500-AH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold


Germany

www.weidmueller.com

Accessories

Type	HDC 16D SLU 1M32G	Version
Order No.	1900900000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, high, without cover, Size of cable entries: M 32
GTIN (EAN)	4032248521128	
Qty.	1 pc(s).	
Type	HDC 06B SDLU 1PG16G	Version
Order No.	1652980000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, Standard, with cover, Size of cable entries: PG 16
GTIN (EAN)	4008190403058	
Qty.	1 pc(s).	
Type	HDC 06B SLU 2PG16G	Version
Order No.	1652760000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, Standard, without cover, Size of cable entries: PG 16
GTIN (EAN)	4008190402839	
Qty.	1 pc(s).	
Type	HDC 16D SLU 2PG21G	Version
Order No.	1652840000	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, high, without cover, Size of cable entries: PG 21
GTIN (EAN)	4008190402914	
Qty.	1 pc(s).	

Size 3



The PUSH IN connection is a direct-insert method of connection. The preprocessed wire can be inserted directly into the wire connection without the need for any tools.

Number of poles: **6**

Rated current: **24 A**

Rated voltage: **500 V**

Nominal voltage acc. to UL/CSA: **600 V AC/DC**
PUSH IN technology

General ordering data

Type	HDC HE 6 MP	Version
Order No.	1873530000	HDC insert, Male, 500 V, 24 A, Number of poles: 6, PUSH IN, Size: 3
GTIN (EAN)	4032248457786	
Qty.	1 pc(s).	