

ZQV 6N/7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

| | |
|------------|--|
| Version | Cross-connector (terminal), Plugged, Number of poles: 7, Pitch in mm (P): 8.00, Insulated: Yes, 41 A, orange |
| Order No. | 2733960000 |
| Type | ZQV 6N/7 |
| GTIN (EAN) | 4064675066804 |
| Qty. | 20 pc(s). |

ZQV 6N/7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | |
|------------|--------|
| Net weight | 9.94 g |
|------------|--------|

Temperatures

| | | | |
|---------------------|----------------|-----------------------|------------------|
| Storage temperature | -25 °C...55 °C | Operating temperature | -60 °C... 130 °C |
|---------------------|----------------|-----------------------|------------------|

Material data

| | | | |
|---------------------------|-------|--------|--------|
| Material | Wemid | Colour | orange |
| UL 94 flammability rating | V-0 | | |

Additional technical data

| | |
|----------------|---------|
| Type of fixing | Plugged |
|----------------|---------|

Cross-connector

| | |
|---------------------------|------|
| Rated current, multi-pole | 41 A |
|---------------------------|------|

Dimensions

| | |
|-----------------|------|
| Pitch in mm (P) | 8 mm |
|-----------------|------|

General

| | |
|-----------------|---|
| Number of poles | 7 |
|-----------------|---|

Rating data

| | |
|---------------|------|
| Rated current | 41 A |
|---------------|------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ECLASS 9.0 | 27-14-11-40 | ECLASS 9.1 | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

Important note

| | |
|---------------------|--|
| Product information | Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400V The voltage reduced to 25V if cut cross connection with blank cut edges are used |
|---------------------|--|

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | Confirmation of Standards EN 45545-2_2020-10 |
| Engineering Data | CAD data – STEP |
| User Documentation | User Manual ZQV 2.5 |
| Catalogues | Catalogues in PDF-format |