

**TS 35X7.5/1.0 2M/CU/BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Copper has the best electrical conductivity of all metals used. The copper rail has the highest short-circuit protection.

**General ordering data**

Version	Terminal rail, Accessories, 35 x 7.5 x 2000 mm, Copper, untreated
Order No.	<a href="#">2731380000</a>
Type	TS 35X7.5/1.0 2M/CU/BK
GTIN (EAN)	4050118810882
Qty.	2 m

**TS 35X7.5/1.0 2M/CU/BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	7.5 mm	Depth (inches)	0.295 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2,000 mm	Width (inches)	78.74 inch
Net weight	540 g		

**Mounting rail**

Length of the terminal rail	max.	2,000 mm
	min.	0 mm
	nominal	2,000 mm
Material	Copper	
Permitted thermal current for PEN function, max.	150 A	
Pre-punched mounting rail	No	
Short circuit strength corresponds to E-Cu wire	50 mm <sup>2</sup>	
Short-time withstand current per second 6 kA according to IEC 60947-7-2		
Slit gap		
Slit length		
Slit width		
Standards	DIN EN 60715	
Surface finish	untreated	
Thickness	1 mm	

**Classifications**

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ECLASS 9.0	27-40-06-02	ECLASS 9.1	27-40-06-02
ECLASS 10.0	27-40-06-02	ECLASS 11.0	27-40-06-02
ECLASS 12.0	27-40-06-02	ECLASS 13.0	27-40-06-02

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## TS 35X7.5/1.0 2M/CU/BK

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

