

IE-C5CS8UG-500**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Bulk stock, copper cable, rigid, 4 x 2 x AWG 24/1, Cat. 5,
green

General ordering data

Version	Installation cable, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), 500 m
Order No.	2762870000
Type	IE-C5CS8UG-500
GTIN (EAN)	4064675030911
Qty.	1 pc(s).
Packaging	on plywood reel

IE-C5CS8UG-500

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	500 m	Length (inches)	19,685.039 inch
Net weight	21,500 g		

Temperatures

Storage temperature	-40 °C...75 °C	Operating temperature	-40 °C...75 °C
Installation temperature	-20 °C...60 °C		

Technical specifications for cable

Halogen	halogen-free, according to IEC 60754-2	Insulation	PE
Number of poles	8	Number of wires	8
Resistance to oils	in accordance with IEC 60811-2-1	Resistance to spread of flame	in accordance with IEC 60332-1, EN 13501-6 class FCa
Sheathing colour	green (RAL 6018)	Test voltage: wire-wire-shield	700 V AC

Cable specific standards

Generic communication cable facilities	EN 50173-1:2007, ISO / IEC 11801:2002
--	---------------------------------------

Standards

Generic communication cable facilities	EN 50173-1:2007, ISO / IEC 11801:2002
--	---------------------------------------

Cable structure

Arrangement of wire cores	Twisted pair	Colour sequence or wires - wire pairs	white - blue, white - orange, white - green, white - brown
Complete shielding	Aluminium foil, Shielding braid made from copper wiring	Cross-section	4*2*AWG 24/1 - 4*2*0.205 mm ²
Insulation	PE	Insulation cross-section	1.04 mm
Number of wires	8	Sheath diameter, max.	6.7 mm
Sheath diameter, min.	6.3 mm	Sheathing colour	green (RAL 6018)
Sheathing material thickness	0.5 mm	Shielding	SF/UTP
Standard designations	IE-5IC4x2xAWG24/1-PUR 02YS(ST)C11Y, SF/UTP	Strands	1
Wire material	Non-insulated copper wire		

Electrical properties of cable

Capacity at 1 kHz	50 nF/km	Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)
Characteristic impedance	100 ± 5 Ω at 100MHz	Delay skew	15 ns/100m
Loop resistance	190 Ω/km	Shield attenuation	65 dB at 100 Mhz
Signal propagation time	4.5 ns/m	Test voltage: wire-wire-shield	700 V AC
Transfer impedance	20 mΩ/m at 1MHz, 10 mΩ/m at 10 MHz, 10 mΩ/m at 30Mhz		

IE-C5CS8UG-500**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Mechanical and material properties of cable**

Abrasion resistance	very good	Colour	green
Halogen	halogen-free, according to IEC 60754-2	Min. bending radius, once only	5 x cable diameter
Min. bending radius, repetitive	10 x cable diameter	Resistance to oils	in accordance with IEC 60811-2-1
Resistance to spread of flame	in accordance with IEC 60332-1, EN 13501-6 class FCa		

Classifications

ETIM 6.0	EC000830	ETIM 7.0	EC003249
ETIM 8.0	EC003249	ETIM 9.0	EC003249
ECLASS 9.0	27-06-18-05	ECLASS 9.1	27-06-90-90
ECLASS 10.0	27-06-18-01	ECLASS 11.0	27-06-18-01
ECLASS 12.0	27-06-18-01	ECLASS 13.0	27-06-18-01

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

IE-C5CS8UG-500

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Detailed drawing

