

**VPUM111SFXV201TXPX10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



PV Protect is the solution for optimum protection of the inverter against overvoltages. The ready-to-connect boxes are available for different system voltages and can be supplied with various arrester types and MPP trackers. Depending on requirements, connection is made via cable glands or WM4C connectors with convenient and reliable PUSH IN connection technology.

**General ordering data**

Version	Surge protection, 1 MPP, Surge protection II, WM4C, 1000 V
Order No.	<a href="#">2764110000</a>
Type	VPUM111SFXV201TXPX10
GTIN (EAN)	4064675014195
Qty.	1 pc(s).

## VPUM1I1SXFV201TXPX10

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	91 mm	Depth (inches)	3.583 inch
Height	160 mm	Height (inches)	6.299 inch
Width	168 mm	Width (inches)	6.614 inch
Net weight	678 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 - 95% rel. humidity		

## Approvals and norms

Approvals	EN 50539-11
-----------	-------------

## Enclosure

Connection type string	Plug WM4C	Enclosure attachment	Via the four holes under the cover screws
Switch disconnecter execution	no switch		

## General data

Protection degree	IP67
-------------------	------

## Inputs

Amount of maximum power points	1 MPP		
DC Input + & -	Wire connection	Type of connection	WM4C plug-in connector
	Cable entry	Number of cable entries	1
Functional earth connector	Cable entry	Number of cable entries	1
	Wire connection	Type of connection	PUSH IN
Fuse type	Neither fuse cartridge nor holder		

## Surge protection DC side

Conditions and requirements	EN 50539-11	Discharge current $I_n$ (8/20 $\mu$ s)	20 kA
Discharge current, max. (8/20 $\mu$ s)	40 kA	Maximum continuous operating voltage DC UCPV mode +/-, -/PE, +/PE	1,100 V
Operating height in the grounded PV system	$\leq 4000$ m	Operating height in ungrounded PV system	$\leq 4000$ m
PV system voltage, max. $U_{cpv}$	1,100 V	Protection level $U_p$ (+/-, -/PE, +/PE)	$\leq 4,2$ kV
Requirements class	Type II	Short-circuit current $I_{SCPv}$	11 kA
Total discharge current $I_{total}$ (8/20 $\mu$ s)	50 kA		

## Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.1	27-13-08-05	ECLASS 10.0	27-13-08-05
ECLASS 11.0	27-13-08-05	ECLASS 12.0	27-17-90-90
ECLASS 13.0	27-17-90-90		

**VPUM1I1SXFV201TXPX10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Tender specification sheets**

## Long specification

Designation 2: VPU PV  
BOX WM4 II 3 1000 1M  
Over voltage protection  
box for inverters with 1  
Mpp tracker, used to pro-  
tect the DC side. Max.  
String voltage Uoc: 1000  
V MPPT1: 1 input, con-  
nection via WM4 C plug-  
in connector, compati-  
ble with cable type TÜV  
2 Pfg 1169/08.07 / EN  
50618:2069 Connec-  
tion of the box in stitch  
without DC switch 1  
surge protection type II  
Connection of function-  
al earth via cable glands  
(8-12mmØ) cable cross-  
section: 16mm<sup>2</sup> Protection  
class: IP65 and IP67 Plas-  
tic enclosure Dimensions  
HxWxD: 168x160x91  
mm According to stan-  
dard, EN 50539-11:  
2013+A1:2014 IEC  
61643-31: 2018

**Important note**

## Product information

The SPD in the box cannot be replaced.

**Approvals**

## Approvals



## ROHS

Conform

**Downloads**Approval/Certificate/Document of Con-  
formity[PV Protect EU Declaration of Conformity](#)

User Documentation

[Manual PV Protect T2](#)

Catalogues

[Catalogues in PDF-format](#)

## VPUM111SXFXV201TXPX10

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany




[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

## Connection diagram



## Connection diagram



## VPUM1I1SXXV201TXPX10

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Crosshead screwdriver Phillips



Crosshead screwdriver, Phillips, SDK PH DIN 5262, ISO 8764/2-PH, output to ISO 8764-PH, ChromTop tip, SoftFinish grip

## General ordering data

Type	SDK PH2	Version
Order No.	<a href="#">9008490000</a>	Screwdriver, Screwdriver
GTIN (EAN)	4032248056484	
Qty.	1 pc(s).	

## Accessories



The dust protection cap "Dustcap VSSO" protects the Weidmüller and type 4 solar connectors against dust and dirt.

The "SafetyClip" protects the Weidmüller solar connectors against unintentional opening and can only be released using the special multi-tool.

## General ordering data

Type	VSSO WM4 C	Version
Order No.	<a href="#">1254870000</a>	Photovoltaics, Flat design
GTIN (EAN)	4050118047479	
Qty.	100 pc(s).	
Type	SAFETY-CLIP WM4 VPE10	Version
Order No.	<a href="#">1328150000</a>	Photovoltaics, Accessories, Locking clip
GTIN (EAN)	4050118238631	
Qty.	10 pc(s).	

**VPUM1I1SXFV201TXPX10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Tools**

- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

**General ordering data**

Type	MULTI-STRIPAX PV	Version
Order No.	<a href="#">1190490000</a>	Photovoltaics, Plug-in connector
GTIN (EAN)	4032248973262	
Qty.	1 pc(s).	

**... for photovoltaic plug-in connectors**

After stripping the insulation, a suitable contact or wire end ferrule can be crimped onto the end of the cable. Crimping forms a secure connection between conductor and contact and has largely replaced soldering. Crimping denotes the creation of a homogeneous, permanent connection between conductor and connecting element. The connection can be made only with high-quality precision tools. The result is a secure and reliable connection both in mechanical and electrical terms. Weidmüller offers a wide range of mechanical crimping tools. Integral ratchets with release mechanisms guarantee optimum crimping. Crimped connections made with Weidmüller tools comply with international standards and regulations.

**General ordering data**

Type	CTF PV WM4	Version
Order No.	<a href="#">1222870000</a>	Photovoltaics, Crimping tool for photovoltaic contacts, Mechanical,
GTIN (EAN)	4050118006254	without interchangeable inserts
Qty.	1 pc(s).	

## VPUM1I1SXFV201TXPX10

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## PV-Stick field connectors



Faster is better. This also applies to the cabling of solar systems. Our handy connectors stay firmly in your grip even in frosty temperatures and can be installed very quickly and easily without a crimping tool.

You don't need crimp contacts and crimping tools and you avoid assembly errors. This saves up to 50% installation time – without affecting quality. The new photovoltaic connectors are TÜV-approved and comply with IEC 62852.

Our "PUSH IN" technology enables safe connections with minimal effort – insert, turn: current!

- 1.500 V DC (DE) / 1,500 V DC (EN)
- PUSH IN technology
- Standard-compliant quality in accordance with IEC 62852
- Ergonomic, prize-winning design
- Fastest PV connector currently available
- Reliable latching

## General ordering data

Type	PV-STICK SET	Version
Order No.	<a href="#">1422030000</a>	Photovoltaics, Plug-in connector, PUSH IN connection, male, female
GTIN (EAN)	4050118225723	
Qty.	1 pc(s).	
Type	PV-STICK- VPE10	Version
Order No.	<a href="#">1303490000</a>	Photovoltaics, Plug-in connector, PUSH IN connection, male
GTIN (EAN)	4050118102529	
Qty.	10 pc(s).	
Type	PV-STICK+ VPE10	Version
Order No.	<a href="#">1303450000</a>	Photovoltaics, Plug-in connector, PUSH IN connection, female
GTIN (EAN)	4050118102468	
Qty.	10 pc(s).	

## X-Connector Cables



The Y or X cable is used to connect three or four elements of a PV system, such as the connection between PV panels, inverters and surge protection boxes. The cables are available in different connection variants.

## General ordering data

Type	PVHXW+W+PXXX06M-15	Version
Order No.	<a href="#">2814290000</a>	Photovoltaics, X-Connector Cable, 2x WM4 C Female, 1x Partly
GTIN (EAN)	4064675298977	stripped cable end, 1x WM4 C Male, 6mm <sup>2</sup> , 1500 V
Qty.	1 pc(s).	

## VPUM1I1SXXFXV201TXPX10

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	PVHXW-W-PXXX06W+15	Version
Order No.	<a href="#">2814280000</a>	Photovoltaics, X-Connector Cable, 2x WM4 C Male, 1x Partly stripped
GTIN (EAN)	4064675298960	cable end, 1x WM4 C Female, 6mm², 1500 V
Qty.	1 pc(s).	
Type	PVHXM+M+W-XX06M-15	Version
Order No.	<a href="#">2814270000</a>	Photovoltaics, X-Connector Cable, 2x MC4 Female, 1x WM4 C Male,
GTIN (EAN)	4064675298953	1x MC4 Male, 6mm², 1000 V
Qty.	1 pc(s).	
Type	PVHXW-W-W+XX06W+15	Version
Order No.	<a href="#">2814240000</a>	Photovoltaics, X-Connector Cable, 2x WM4 C Male, 2x WM4 C
GTIN (EAN)	4064675298922	Female, 6mm², 1500 V
Qty.	1 pc(s).	
Type	PVHXM-M-W+XX06M+15	Version
Order No.	<a href="#">2814260000</a>	Photovoltaics, X-Connector Cable, 2x MC4 Male, 1x WM4 C Female,
GTIN (EAN)	4064675298946	1x MC4 Female, 6mm², 1000 V
Qty.	1 pc(s).	
Type	PVHXW+W+W-XX06W-15	Version
Order No.	<a href="#">2814250000</a>	Photovoltaics, X-Connector Cable, 2x WM4 C Female, 2x WM4 C
GTIN (EAN)	4064675298939	Male, 6mm², 1500 V
Qty.	1 pc(s).	

## Y-Connector Cables



The Y or X cable is used to connect three or four elements of a PV system, such as the connection between PV panels, inverters and surge protection boxes. The cables are available in different connection variants.

## General ordering data

Type	PVHYM+XXW-XX06M-15	Version
Order No.	<a href="#">2814210000</a>	Photovoltaics, Y-Connector Cable, 1x MC4 Female, 1x WM4 C Male,
GTIN (EAN)	4064675298892	1x MC4 Male, 6mm², 1000 V
Qty.	1 pc(s).	
Type	PVHYW-XXPXXX06W+15	Version
Order No.	<a href="#">2814220000</a>	Photovoltaics, Y-Connector Cable, 1x WM4 C Male, 1x Partly stripped
GTIN (EAN)	4064675298908	cable end, 1x WM4 C Female, 6mm², 1500 V
Qty.	1 pc(s).	
Type	PVHYW+XXW-XX06W-15	Version
Order No.	<a href="#">2814190000</a>	Photovoltaics, Y-Connector Cable, 1x WM4 C Female, 2x WM4 C
GTIN (EAN)	4064675298878	Male, 6mm², 1500 V
Qty.	1 pc(s).	
Type	PVHYW-XXW+XX06W+15	Version
Order No.	<a href="#">2814180000</a>	Photovoltaics, Y-Connector Cable, 1x WM4 C Male, 2x WM4 C
GTIN (EAN)	4064675298861	Female, 6mm², 1500 V
Qty.	1 pc(s).	



**VPUM1I1SXFV201TXPX10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories**

Type	PVHYM-XXW+XX06M+15	Version
Order No.	<a href="#">2814200000</a>	Photovoltaics, Y-Connector Cable, 1x MC4 Male, 1x WM4 C Female,
GTIN (EAN)	4064675298885	1x MC4 Female, 6mm <sup>2</sup> , 1000 V
Qty.	1 pc(s).	