

**SAIH-SLL-3X0.75-16X0.34-500****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Weidmüller can supply suitable bus lines for customising. All bus cables are suitable for moving cable carriers and are available by the metre. The colour coding of the lines corresponds to the standard in mechanical engineering. The connection hoods of the M12 distributor always have the same number of terminals so that only one type of cable is necessary.

Advantages of bus cables supplied by the metre:

- Special lengths for bus cables
- No cable waste
- No storage space required for different cable lengths
- Also available in specific lengths.

**General ordering data**

|            |  |
|------------|--|
| Version    | Sensor/actuator line, Number of poles: 19, 500 m, Shielded: No, LED: No, Sheath material: PUR, Halogen: No |
| Order No.  | <a href="#">2764960000</a>   |
| Type       | SAIH-SLL-3X0.75-16X0.34-500  |
| GTIN (EAN) | 4064675031253  |
| Qty.       | 1 pc(s).   |
| Packaging  | on plywood reel  |

Creation date May 2, 2024 12:33:41 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

**SAIH-SLL-3X0.75-16X0.34-500**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 63.373 g

**Technical specifications for cable**

|                                      |  |  |  |
|--------------------------------------|--|--|--|
| Acceleration                         | 5 m/s <sup>2</sup>                                   | Bending cycles                                 | 2 Mio  |
| Bending radius, min., moving         | 10 x cable diameter                                  | Bending radius, min., stationary               | 5 x cable diameter   |
| Cable length                         | 500 m  | Colour coding                                  | violet, red, grey, red / blue, green, blue, grey / pink, white / green, white / yellow, white / grey, black, Green/yellow, Yellow / brown, brown / green, white, yellow, pink, grey / brown, brown |
| Core in accordance with UL AWM style | 10493 (80 °C / 300 V)                                | Halogen  | No   |
| Insulation                           | TPM  | Number of poles                                | 19   |
| Number of wires                      | 19   | Outer cladding in accordance with UL AWM style | 21198 (80 °C / 300 V)  |
| Outside diameter                     | 9.1 mm ± 0.3 mm                                      | Resistance to oils                             | Yes  |
| Resistant to welding beads           | No   | Sheath material                                | PUR  |
| Sheathing colour                     | black  | Shielded                                       | No   |
| Speed                                | 200 m/s  | Suitable for cable carriers                    | Yes  |
| Temperature range, moving            | -25...80 °C  | Temperature range, stationary                  | -50...80 °C  |
| Torsion resistance                   | 0 °/m  | Welding spark resistance                       | No   |
| Wire cross section (Print/Online)    | 3 x 0.75 mm <sup>2</sup> + 16 x 0.34 mm <sup>2</sup> |  |  |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001578    | ETIM 7.0    | EC003250    |
| ETIM 8.0    | EC003250    | ETIM 9.0    | EC003250    |
| ECLASS 9.0  | 27-06-20-11 | ECLASS 9.1  | 27-06-90-90 |
| ECLASS 10.0 | 27-06-01-06 | ECLASS 11.0 | 27-06-01-06 |
| ECLASS 12.0 | 27-06-01-06 | ECLASS 13.0 | 27-06-01-06 |

**Approvals**

Approvals



ROHS Conform

**Downloads**

Catalogues [Catalogues in PDF-format](#)

## SAIH-SLL-3X0.75-16X0.34-500

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Screwty® cable gland tool with torque function



## The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

## General ordering data

|            |                            |              |  |
|------------|----------------------------|--------------|--|
| Type       | 1/4" HANDGRIFF             | Version      |  |
| Order No.  | <a href="#">4294820000</a> | Bolting tool |  |
| GTIN (EAN) | 4032248478279              |              |  |
| Qty.       | 1 pc(s).                   |              |  |

## Screwty for M23 moulded cables and customisable connectors



The Screwty® attachment is suitable for customisable M23 round plug-in connectors and for overmoulded M23 round plug-in connectors, with an outside dimension of the knurled nut of  $26.2 \pm 0.3$  mm. The tightening torque is 2-2.5 Nm.

## General ordering data

|            |                            |   |  |             |
|------------|----------------------------|---|--|-------------|
| Type       | SCREWTY M23                | Version   |  | Packaging   |
| Order No.  | <a href="#">1981560000</a> | Cable gland tool adapter for M23 lines and connectors |  | Plastic bag |
| GTIN (EAN) | 4032248677702              |   |  |             |
| Qty.       | 1 pc(s).                   |   |  |             |