

WIL-LWXXXX-4000D024-240SX10.0BXXXXXXXXXX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The WIL-LED lights family: Only 8mm (9.4mm with magnet) high LED lamp for 24V DC with very high luminous efficacy and high Lifespan (greater 60 000h). Very robust construction, by full potting and metal housing - waterproof (IP67). Due to its 4000K light color, neutral white, suitable for the various applications. Very easy to connect thanks to the M12 connection. Due to the low power consumption, a small enough power supply with 24V for operation.

General ordering data

Order No.	2770730000
Type	WIL-LWXXXX-4000D024-240SX10.0BXXXXXXXXXX
GTIN (EAN)	4064675030799
Qty.	1 pc(s).

WIL-LWXXXX-4000D024-240SX10.0BXXXXXXXXXX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	40 mm	Depth (inches)	1.575 inch
Height	8 mm	Height (inches)	0.315 inch
Width	240 mm	Width (inches)	9.449 inch
Net weight	240 g		

Temperatures

Operating temperature	-20 - 60°C
-----------------------	------------

Cable technical specifications

Cable Material	PUR	Sheathing colour	black
Cable length	10 m		

Connection data

Version	Cable end open	Connection thread	without
Coding		Wiring	Pin 4 (Strand: black) control white LED, Pin 3 (Strand: blue)
	A-coded		

Electric data

Rated voltage	24 V DC	Rated current	0.308 A
Power	7.4 W	Dimmable	Yes

General technical data

Electronic equipment on rolling stock	No	Recommended class according to UL for use of an power supply	NEC Class 2
Shape of the LED module	Rectangular	Type of connection	Pre-assembled cable
Number of LEDs	42	Light colour (CCT)	4000K, Neutral white
Luminosity	260 cd	Light current	746 lm
Emitting angle	40 °	Illumination level	260 lux
Operating life	60.000 h	Type of mounting	Screw mounting
Drill hole spacing	225 mm	Impact resistance	IK05
Protection degree	IP67	Efficiency class (according to EU Directive No. 874/2012)	F

Material data

Housing main material	hard anodised aluminium	Encapsulation compound	PUR V0
Material of end caps	Diecast zinc, nickel-plated		

Classifications

ETIM 6.0	EC000996	ETIM 7.0	EC000996
ETIM 8.0	EC000996	ETIM 9.0	EC000996
ECLASS 9.1	27-11-06-35	ECLASS 10.0	27-11-06-35
ECLASS 11.0	27-11-06-35	ECLASS 12.0	27-11-06-35
ECLASS 13.0	27-11-06-35		

Environmental Product Compliance

EPREL Registration number	1324559
---------------------------	---------

Creation date April 29, 2024 7:16:12 PM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

WIL-LWXXXX-4000D024-240SX10.0BXXXXXXXXXX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E354496

Downloads

Engineering Data	CAD data – STEP
User Documentation	Designation key WIL Flyer WIL
Catalogues	Catalogues in PDF-format


WIL-LWXXXX-4000D024-240SX10.0BXXXXXXXXXX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



WIL-LWXXXX-4000D024-240SX10.0BXXXXXXXXXX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Magnet**

Magnet for WIL lights with 240mm total length, self-adhesive

Magnet**General ordering data**

Type	WIL-MAGNET
Order No.	2526810000
GTIN (EAN)	4050118537871
Qty.	1 pc(s).

Door switch

The WIL door switch is pre-assembled with an M12 cable and an access line. This allows for a simple Plug and Produce feature with our WIL LED lamp series.

Door Switch**General ordering data**

Type	WIL-TS-M12
Order No.	2537730000
GTIN (EAN)	4050118549188
Qty.	1 pc(s).

WIL-LWXXXX-4000D024-240SX10.0BXXXXXXXXXX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

PUR halogen-free black (U)



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

Type	SAIL-M12BG-3-3.0U	Version
Order No.	9457820300	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4032248228195	poles : 3, 3 m, Female socket, straight, Shielded: No, LED: No, Sheath
Qty.	1 pc(s).	material: PUR, Halogen: No

Motion sensor Jackpac®



Motion detector for the WIL-LED luminaire with screw connection, 3m supply cable and M12 cable for connection to the WIL lamp. Switching time adjustable.

General ordering data

Type	WIL-BM-JP-M12-3.0U
Order No.	2537710000
GTIN (EAN)	4050118549164
Qty.	1 pc(s).

WIL-LWXXXX-4000D024-240SX10.0BXXXXXXXXXX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Straight**

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

General ordering data

Type	SAIS-4/7	Version
Order No.	9457550000	Field attachable connector, M12, pin, straight
GTIN (EAN)	4032248167647	
Qty.	1 pc(s).	
Type	SAIB-4/7	Version
Order No.	9457240000	Field attachable connector, M12, Female socket, straight
GTIN (EAN)	4008190312275	
Qty.	1 pc(s).	

WIL-LWXXXX-4000D024-240SX10.0BXXXXXXXXXX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

PUR halogen-free black (U)



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

The M8 and M12 sensor-actuator cables are supplied as standard with brass nickel-plated nuts. However if you are looking to use our products in an extremely harsh environment, we can also supply a variant with a plastic nut. This enables use in environments where cables with nickel-plated M8 and M12 nuts would rust.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

Type	SAIP-M12BG-3-3.0U	Version
Order No.	1108730300	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4032248888481	poles : 3, 3 m, Female socket, straight, Shielded: No, LED: No, Sheath
Qty.	1 pc(s).	material: PUR, Halogen: No

Motion sensor screw connection



Motion detector for the WIL-LED luminaire with screw connection. Switching time adjustable.

General ordering data

Type	WIL-BM-SK
Order No.	2537720000
GTIN (EAN)	4050118549157
Qty.	1 pc(s).

WIL-LWXXXX-4000D024-240SX10.0BXXXXXXXXXX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Motion sensor screw connection with cable



Motion detector for the WIL-LED luminaire with screw connection, 3m supply cable and M12 cable for connection to the WIL lamp. Switching time adjustable.

General ordering data

Type	WIL-BM-SK-M12-3.0U
Order No.	2537700000
GTIN (EAN)	4050118549140
Qty.	1 pc(s).

Swivelling holder



Swivel bracket for WIL lights Very high quality version without detent

Swivelling holder

General ordering data

Type	WIL-SCHWENKHALTER
Order No.	2614220000
GTIN (EAN)	4050118651249
Qty.	1 pc(s).

WIL-LWXXXX-4000D024-240SX10.0BXXXXXXXXXX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

WIL power supply



Power supply IP65 for WIL standard family 85V-264V AC input, 24V DC output 400mA

Power Supply

General ordering data

Type	WIL-NT-STANDARD
Order No.	2598350000
GTIN (EAN)	4050118611168
Qty.	1 pc(s).

Connect Power INSTA POWER



The single-phase INSTA-POWER switching power supplies are characterised by a wide power spectrum, compact design and good value for money. They are suitable for temperature ranges from -25°C to +70°C, have international approvals and a wide voltage input range. This makes them suitable for a wide range of applications. This also includes signal and telecommunications systems as well as automation systems with a low power requirement up to 96 Watt.

General ordering data

Type	PRO INSTA 30W 24V 1.3A	Version
Order No.	2580190000	Power supply, switch-mode power supply unit, 24 V
GTIN (EAN)	4050118590920	
Qty.	1 pc(s).	

WIL-LWXXXX-4000D024-240SX10.0BXXXXXXXXXX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

