

**HDC C HS BM0.2-0.5 AU****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

**General ordering data**

Version	Female, gold, 0.2 - 0.5 mm <sup>2</sup>
Order No.	<a href="#">2748720000</a>
Type	HDC C HS BM0.2-0.5 AU
GTIN (EAN)	4050118890631
Qty.	100 pc(s).

**HDC C HS BM0.2-0.5 AU****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	0.22 g
------------	--------

**Temperatures**

Limit temperature	-55 °C ... 130 °C
-------------------	-------------------

**General data**

Conductor cross-section, max.	0.5 mm <sup>2</sup>	Conductor cross-section, min.	0.2 mm <sup>2</sup>
Contact diameter, male Ø	1 mm	Cross-section for connected wire	0.2 - 0.5 mm <sup>2</sup>
Material	Copper alloy	Series	ModuPlug
Surface finish	gold	Type	Female
Type of connection	Crimp connection		

**Classifications**

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ETIM 9.0	EC000796
ECLASS 9.0	27-44-02-04	ECLASS 9.1	27-44-02-04
ECLASS 10.0	27-44-02-04	ECLASS 11.0	27-44-02-04
ECLASS 12.0	27-44-02-04	ECLASS 13.0	27-44-02-04

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Manual GigaBit Module</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>