

**SAIB-M-4S-IDC-M12-D-COD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

M12 plug-in connector in IP 67 available with crew or tension clamp connection

**General ordering data**

Version	Field attachable connector, M12
Order No.	<a href="#">2812410000</a>
Type	SAIB-M-4S-IDC-M12-D-COD
GTIN (EAN)	4064675295228
Qty.	1 pc(s).

## SAIB-M-4S-IDC-M12-D-COD

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	26.1 g
------------	--------

## Technical data customisable plug-in connectors

Cable diameter	5...9.7 mm	Cable diameter, max.	9.7 mm
Cable diameter, min.	5 mm	Coding	D-coded
Conductor cross-section, max.	0.34 mm <sup>2</sup>	Conductor cross-section, min.	0.14 mm <sup>2</sup>
Connection cross-section, max.	0.34 mm <sup>2</sup>	Connection cross-section, min.	0.14 mm <sup>2</sup>
Contact surface	Gold-plated	Housing main material	zinc diecast nickel-plated
Number of poles	4	Plugging cycles	≥ 100
Pollution severity	3	Protection degree	IP67
Rated current	4 A	Rated voltage	250 V
Shield connection	Yes	Temperature range of housing	-40 ... +85 °C
Threaded ring material	Diecast zinc	Type of connection	Insulation displacement connection

## General Info

Number of poles	4	Connection 1	M12
Connection 2	IDC	Housing main material	zinc diecast nickel-plated
Insulation cross-section, max.	1.6	Connection thread	M12
Contact surface	Gold-plated	Wire connection diameter, solid, min.	0.4
Wire connection diameter, solid, max.	0.64	Wire cross-section, solid, min. (AWG)	AWG 24/1
Wire cross-section, solid, max. (AWG)	AWG 22/1	Wire connection diameter, flexible, min.	0.48 mm
Wire connection diameter, flexible, max.	0.76 mm	Wire cross-section, finely stranded, min. (AWG)	AWG 26/7
Wire cross-section, finely stranded, max. (AWG)	AWG 22/7	Sheath diameter, min.	5 mm
Sheath diameter, max.	9.7 mm	Protection degree	IP67
Plugging cycles	≥ 100		

## Electrical properties

Rated voltage	250 V
---------------	-------

## General standards

Connector standard	IEC 61076-2-101
--------------------	-----------------

## Standards

Connector standard	IEC 61076-2-101
--------------------	-----------------

## Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

Creation date May 20, 2024 5:23:11 PM CEST

## SAIB-M-4S-IDC-M12-D-COD

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

Approvals



ROHS

Conform

### Downloads


Catalogues

[Catalogues in PDF-format](#)

**SAIB-M-4S-IDC-M12-D-COD**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings****Dimensioned drawing****Pinning**