

**RCMA-B22-D70-6.0****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Rogowski coil**

A Rogowski coil is a closed air coil without a ferromagnetic core used for floating potential measurement of AC and pulse currents. Measurement with the Rogowski coil is used widely in technology, as it can be retroactively integrated without separating the primary electric circuit in existing systems. Because this method shows no saturation effect, even the smallest currents and high-frequency harmonics can be measured without loss of accuracy.

**General ordering data**

Version	Rogowski coil, Diameter: 70 mm, Cable length: 6 m, 100...5000 A, Output : Pulse, mV signal
Order No.	<a href="#">2831090000</a>
Type	RCMA-B22-D70-6.0
GTIN (EAN)	4064675395683
Qty.	1 pc(s).

## RCMA-B22-D70-6.0

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Diameter	70 mm	Net weight	312 g
----------	-------	------------	-------

## Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Humidity at operating temperature	5 - 90 %, no condensation		

## Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	70 mm
Installation location	Indoor use		

## Electrical attributes

Frequency band	50...60 Hz	Measurement error	<± 0.5% (of measuring range limit)
Nominal turns ratio	44.44 kA/V	Phase shift	0.004 °
Primary current	5,000 A	Secondary voltage	22.5 mV (@ 50Hz I <sub>primary</sub> = 1 kA), 30 V (max)
Tolerance class	0,5		

## Technical properties

Cable diameter	6.1 mm	Cable length	6 m
Coil resistance	81 Ω	Protection degree	IP57

## Input

Outer cable diameter, max.	70 mm
----------------------------	-------

## General data

Linearity	no linearity error
-----------	--------------------

## Insulation coordination

Impulse withstand voltage	12.8 kV (1.2/50 ms)	Insulation voltage	7.4 kV <sub>RMS</sub> (50 Hz, 1 min)
Pollution severity	2	Rated insulation voltage	1 kV <sub>rms</sub>
Surge voltage category	III	Tolerance class	0,5
Tracking resistance (CTI)	600		

## Classifications

ETIM 6.0	EC002475	ETIM 7.0	EC002475
ETIM 8.0	EC002475	ETIM 9.0	EC002475
ECLASS 9.0	27-21-01-23	ECLASS 9.1	27-21-01-23
ECLASS 10.0	27-21-01-23	ECLASS 11.0	27-21-01-23
ECLASS 12.0	27-21-01-23	ECLASS 13.0	27-21-01-23

**RCMA-B22-D70-6.0****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

Approvals



ROHS Conform

UL File Number Search UL Website

Certificate No. (cURus) E469563

**Downloads**Approval/Certificate/Document of Con-  
formity[Declaration of Conformity](#)

User Documentation

[Instruction sheet](#)

Catalogues

[Catalogues in PDF-format](#)

## RCMA-B22-D70-6.0

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

