

CA-T2WB-5.5M-7.4/1P-R-BBG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The Mode 3 charging cables with ergonomic handle design offer charging comfort of the highest quality. Robust and durable in every respect: the housing is dirt and water repellent, shock and impact resistant as well as cold and heat resistant. Available in different lengths, in straight and spiral form, for 1- or 3-phase charging.

General ordering data

| | |
|------------|--|
| Version | AC charging cable, Connection type - charging point: free conductor end, Connection type - vehicle: Type 2, Charging power, max.: 7.4 kW, Number of phases: 1, Rated current: 32 A, Cable length: 5.5 m, Cable type: regular |
| Order No. | 2861570000 |
| Type | CA-T2WB-5.5M-7.4/1P-R-BBG |
| GTIN (EAN) | 4064675581468 |
| Qty. | 1 pc(s). |

Creation date May 20, 2024 4:01:19 AM CEST

Catalogue status 04.05.2024 / We reserve the right to make technical changes.

CA-T2WB-5.5M-7.4/1P-R-BBG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|----------|---------|------------|---------|
| Diameter | 13.7 mm | Net weight | 3,560 g |
|----------|---------|------------|---------|

Temperatures

| | |
|-----------------------|----------------|
| Operating temperature | -30 °C...55 °C |
|-----------------------|----------------|

Cable

| | | | |
|--------------|---------|--------------|-------|
| Cable colour | black | Cable length | 5.5 m |
| Cable type | regular | | |

Plug type

| | | | |
|----------------------------------|--------------------|---------------------------|--------|
| Connection type - charging point | free conductor end | Connection type - vehicle | Type 2 |
| Plug colour | black, dark grey | | |

System requirements

| | |
|----------------------------------|---|
| Type of communication to vehicle | Control Pilot (CP), Proximity Pilot / Plug Present (PP) |
|----------------------------------|---|

Material data

| | | | |
|-----------------------------|-------|-----------------------------|--------|
| Operating temperature, max. | 55 °C | Operating temperature, min. | -30 °C |
|-----------------------------|-------|-----------------------------|--------|

Features

| | |
|-------------------|------|
| Protection degree | IP54 |
|-------------------|------|

Housing

| | |
|-------------------|------|
| Protection degree | IP54 |
|-------------------|------|

Approvals and norms

| | |
|-----------|------------------------------------|
| Approvals | IEC 62196-1, IEC 62196-2, EN 50620 |
|-----------|------------------------------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002897 | ETIM 7.0 | EC002897 |
| ETIM 8.0 | EC002897 | ETIM 9.0 | EC002897 |
| ECLASS 9.0 | 27-14-47-05 | ECLASS 9.1 | 27-14-47-05 |
| ECLASS 10.0 | 27-14-47-05 | ECLASS 11.0 | 27-14-47-05 |
| ECLASS 12.0 | 27-14-47-05 | ECLASS 13.0 | 27-14-47-05 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | f233b551-8efc-4a5f-b233-33b40f22269a |

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|