

FUSEHOLDER WSFH/2 10X38 1KV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Photovoltaic fuse holder for PV applications**

- For usage in photovoltaic DC combiner boxes up to 1000V
- DIN- rail mounted
- For use with cylindrical fuse links from 1A up to 30A of 10x38mm gPV

General ordering data

| | |
|------------|---|
| Version | Photovoltaics, Fuse holder, 1000 V, 10x38, 2 Strings, Without LED |
| Order No. | 2896940000 |
| Type | FUSEHOLDER WSFH/2 10X38 1KV |
| GTIN (EAN) | 4064675899662 |
| Qty. | 5 pc(s). |

FUSEHOLDER WSFH/2 10X38 1KV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|-------|-----------------|------------|
| Depth | 61 mm | Depth (inches) | 2.402 inch |
| Height | 73 mm | Height (inches) | 2.874 inch |
| Width | 18 mm | Width (inches) | 0.709 inch |
| Net weight | 96 g | | |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|-------|
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 90 °C |
|----------------------------------|--------|----------------------------------|-------|

Fuse holder connection

| | | | |
|---|--------------------|---|-------------------|
| Number of connections | 2 | Stripping length | 10 mm |
| Tightening torque, max. | 2.5 Nm | Tightening torque, min. | 2 Nm |
| Type of connection | Screw connection | Wire connection cross section AWG, max. | AWG 17 |
| Wire connection cross section AWG, min. | AWG 6 | Wire connection cross section, finely stranded, min. | 1 mm ² |
| Wire connection cross section, finely stranded, max. | 10 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 1 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 10 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 1 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 10 mm ² | Wire connection cross-section, solid core, min. | 1 mm ² |
| Wire connection cross-section, solid core, max. | 10 mm ² | Wire material | Copper |

Fuse holder technical data

| | | | |
|--------------------------------|------------|---------------------------------|-------------|
| Type of mounting | Rail | Cartridge fuse | 10 x 38 mm |
| Colour | Light Blue | Display | Without LED |
| Fuse holder (cartridge holder) | Pivoting | Max. current | 30 A |
| Number of potentials | 1 | Power dissipation, max. | 3 W |
| Rail | TS 35 | Rated impulse withstand voltage | 6 kV |
| Surge voltage category | III | Operating voltage, max. | 1000 V |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000899 | ETIM 7.0 | EC000899 |
| ETIM 8.0 | EC000899 | ETIM 9.0 | EC000899 |
| ECLASS 9.0 | 27-14-11-16 | ECLASS 9.1 | 27-14-11-16 |
| ECLASS 10.0 | 27-14-11-16 | ECLASS 11.0 | 27-14-11-16 |
| ECLASS 12.0 | 27-14-11-16 | ECLASS 13.0 | 27-25-01-13 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | Declaration of Conformity for PV fuse holders |
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |


Creation date May 10, 2024 4:15:38 PM CEST

FUSEHOLDER WSFH/2 10X38 1KV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



FUSEHOLDER WSFH/2 10X38 1KV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

10x38 gPV



The gPV cylindrical fuse cartridges are designed to provide compact, safe and economical protection of photovoltaic modules (field protection) with voltages up to 1,500 DC. They provide protection against both overload and short circuit (gPV class according to the requirements of IEC60269-6 and UL248-19 standards). Made of a ceramic tube with high internal pressure and thermal shock resistance, allowing high switching capacity in a small space. The contacts are made of silver-plated copper and the fusible elements of pure silver to avoid ageing and thus keep the electrical characteristics invariable. They are available in the sizes 10x38 mm, 10x85 mm and 22x58 mm.

General ordering data

| | | |
|------------|-----------------------------|---|
| Type | FUSE 10X38 5A 1000 VDC ... | Version |
| Order No. | 2783200000 | Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 5 A |
| GTIN (EAN) | 4064675059929 | |
| Qty. | 10 pc(s). | |
| Type | FUSE 10X38 4A 1000 VDC ... | Version |
| Order No. | 2783190000 | Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 4 A |
| GTIN (EAN) | 4064675059912 | |
| Qty. | 10 pc(s). | |
| Type | FUSE 10X38 15A 1000 VDC ... | Version |
| Order No. | 2783250000 | Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 15 A |
| GTIN (EAN) | 4064675059974 | |
| Qty. | 10 pc(s). | |
| Type | FUSE 10X38 12A 1000 VDC ... | Version |
| Order No. | 2783240000 | Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 12 A |
| GTIN (EAN) | 4064675059967 | |
| Qty. | 10 pc(s). | |
| Type | FUSE 10X38 3A 1000 VDC ... | Version |
| Order No. | 2783180000 | Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 3 A |
| GTIN (EAN) | 4064675059905 | |
| Qty. | 10 pc(s). | |
| Type | FUSE 10X38 10A 1000 VDC ... | Version |
| Order No. | 2783230000 | Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 10 A |
| GTIN (EAN) | 4064675059950 | |
| Qty. | 10 pc(s). | |
| Type | FUSE 10X38 6A 1000 VDC ... | Version |
| Order No. | 2783210000 | Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 6 A |
| GTIN (EAN) | 4064675059936 | |
| Qty. | 10 pc(s). | |
| Type | FUSE 10X38 8A 1000 VDC ... | Version |
| Order No. | 2783220000 | Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 8 A |
| GTIN (EAN) | 4064675059943 | |
| Qty. | 10 pc(s). | |
| Type | FUSE 10X38 20A 1000 VDC ... | Version |
| Order No. | 2783280000 | Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 20 A |
| GTIN (EAN) | 4064675060000 | |
| Qty. | 10 pc(s). | |

FUSEHOLDER WSFH/2 10X38 1KV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

| | | |
|------------|-----------------------------|---|
| Type | FUSE 10X38 2A 1000 VDC ... | Version |
| Order No. | 2783170000 | Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 2 A |
| GTIN (EAN) | 4064675059691 | |
| Qty. | 10 pc(s). | |
| Type | FUSE 10X38 30A 1000 VDC ... | Version |
| Order No. | 2828000000 | Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 30 A |
| GTIN (EAN) | 4064675367826 | |
| Qty. | 10 pc(s). | |
| Type | FUSE 10X38 16A 1000 VDC ... | Version |
| Order No. | 2783260000 | Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 16 A |
| GTIN (EAN) | 4064675059981 | |
| Qty. | 10 pc(s). | |
| Type | FUSE 10X38 1A 1000 VDC ... | Version |
| Order No. | 2783160000 | Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 1 A |
| GTIN (EAN) | 4064675059684 | |
| Qty. | 10 pc(s). | |
| Type | FUSE 10X38 25A 1000 VDC ... | Version |
| Order No. | 2827990000 | Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 25 A inline fuse |
| GTIN (EAN) | 4064675367819 | |
| Qty. | 10 pc(s). | |