

PZ 2.5 S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	0.14mm ² , 2.5mm ² , Trapezoidal crimp
Order No.	2903690000
Type	PZ 2.5 S
GTIN (EAN)	4099986027008
Qty.	1 pc(s).

PZ 2.5 S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	31 mm	Depth (inches)	1.22 inch
Height	70 mm	Height (inches)	2.756 inch
Width	160 mm	Width (inches)	6.299 inch
Length	160 mm	Length (inches)	6.299 inch
Net weight	290.6 g		

Technical data

Version	Mechanical, without inter-changeable inserts
---------	--

Description of contact

Conductor cross-section, max. AWG	AWG 14	Conductor cross-section, min. AWG	AWG 26
Crimping range, max.	2.5 mm ²	Crimping range, min.	0.14 mm ²
Type of contact	Wire-end ferrules with/ without plastic collars		

tool data crimping

Crimping type/profile	Trapezoidal crimp	Wire end ferrules cross-section, max.	2.5 mm ²
Wire end ferrules cross-section, min.	0.14 mm ²		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ECLASS 9.0	21-04-38-11	ECLASS 9.1	21-04-38-11
ECLASS 10.0	21-04-38-11	ECLASS 11.0	21-04-38-11
ECLASS 12.0	21-04-38-11	ECLASS 13.0	21-04-38-11

Downloads

User Documentation	BDAL PZ 2.5
Catalogues	Catalogues in PDF-format