

ACT20D-LCD-CI-ILP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Suitable for field mounting to display an analog 4- 20 mA signal.

The digital indicator is looped into the current loop.

Features:

- No separate supply voltage is required.
- For industrial environments, mounted in the control cabinet door, the protection class is IP65.
- Even in unfavourable lighting conditions, the display value is clearly visible.

General ordering data

Version	Display, Input : 4-20 mA, (loop powered), Output : Display
Order No.	2920000000
Type	ACT20D-LCD-CI-ILP
GTIN (EAN)	4099986580336
Qty.	1 pc(s).

ACT20D-LCD-CI-ILP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	120 mm	Depth (inches)	4.724 inch
Height	48.8 mm	Height (inches)	1.921 inch
Width	96.6 mm	Width (inches)	3.803 inch
Net weight	262 g		

Temperatures

Storage temperature	-20 °C...85 °C	Operating temperature	-20 °C...60 °C
Humidity	0...95 % (no condensation)		

Display

Adjustment of display backlighting	0%, 50%, 100%	Decimal point	18888, 1.8888, 18.888, 188.88, 1888.8
Dimmable	Yes	Display range	-9999...9999
Display value	Current	Scaling	Variable
Type	4-character, LCD display, 16 mm		

General data

Accuracy	<0.1 % of measuring range	Configuration	Front push-button, DIP switch to lock / unlock the front push-button
DIN Rail compatibility	No	Protection degree	IP20, IP65 (in plugged condition), IP65
Step response time	≤1s	Type of connection	Tension clamp connection with actuator
Type of mounting	Frontpanel mounting, Front mounting	Voltage supply	Loop powered, via 4...20 mA input

Input

Input current	4...20mA	Input measurement range	3.6 ... 23 mA (NAMUR NE43 conform)
Number of inputs	1	Response time	≤ 1 s
Sensor	Current source	Voltage drop, current input	without backlight <1.5 V @ 20 mA, half backlight <6.5 V @ 20 mA, full backlight <10.5 V @ 20 mA

Output (digital)

Contact material	Cu
------------------	----

Connection data

Wire connection method	Screw connection	Type of connection	Tension clamp connection with actuator
Wire connection cross section AWG, min.	AWG 26	Wire connection cross section AWG, max.	AWG 14
Wire connection cross section, finely stranded, min.	0.13 mm ²	Wire connection cross section, finely stranded, max.	2.8 mm ²

ACT20D-LCD-CI-ILP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Classifications

ETIM 6.0	EC000677	ETIM 7.0	EC000677
ETIM 8.0	EC000677	ETIM 9.0	EC000677
ECLASS 9.0	27-14-31-10	ECLASS 9.1	27-21-03-01
ECLASS 10.0	27-14-31-10	ECLASS 11.0	27-14-31-10
ECLASS 12.0	27-14-31-10	ECLASS 13.0	27-14-31-10

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	f4905d12-f516-4eb5-90a8-8c87685bc956

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	RCM certification Declaration of Conformity
User Documentation	Instruction sheet
Catalogues	Catalogues in PDF-format


ACT20D-LCD-CI-ILP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings


Dimensioned drawing



Wiring diagram



Menu



ACT20D-LCD-CI-ILP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Process value indicators with LED display - ACT20D**

Devices in this series display universal analogue process values.

Depending on the version, the devices convert/isolate the signals into an analogue current signal and have additional limit value relays which switch further signals. Features:

- Several sensor variants can be processed.
- An auxiliary power supply is required.
- Even in unfavourable lighting conditions, the display value is clearly visible.

General ordering data

Type	PROTECTIVE COVER	Version
Order No.	2964330000	Display, Hood
GTIN (EAN)	4099986768086	
Qty.	1 pc(s).	