

ACT20D-LED-FI-AO-2RC-AC-DC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Devices in this series display universal analogue process values.

Depending on the version, the devices convert/isolate the signals into an analogue current signal and have additional limit value relays which switch further signals.

Features:

- Several sensor variants can be processed.
- An auxiliary power supply is required.
- Even in unfavourable lighting conditions, the display value is clearly visible.

General ordering data

Version	Display, Input : Frequency, Output : Display, analogue V / mA, 2 x relays
Order No.	2920070000
Type	ACT20D-LED-FI-AO-2RC-AC-DC
GTIN (EAN)	4099986580367
Qty.	1 pc(s).

ACT20D-LED-FI-AO-2RC-AC-DC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	120 mm	Depth (inches)	4.724 inch
Height	48.8 mm	Height (inches)	1.921 inch
Width	96.6 mm	Width (inches)	3.803 inch
Net weight	295 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-20 °C...60 °C
---------------------	----------------	-----------------------	----------------

Display

Cycle time	2.2 times / s	Decimal point	configurable, 9.999, 99.99, 999.9, 9999
Dimmable	Yes	Display range	-1999...9999
Display value	current measured value, Percentage or real value display, Switching status	Format	14 segment (numbers + letters), Scrolling text in 8 languages in case of error (e.g. sensor wire breakage, input overrange...)
Scaling	Variable	Type	red LED, 4-character display, Digit size: 13.8 mm

General data

Accuracy	absolute accuracy: $\leq \pm 0.1$ % of the measurement range	Configuration	Front push-button
DIN Rail compatibility	No	Power consumption	≤ 3.5 W
Protection degree	IP20, IP65 (in plugged condition), IP65	Temperature coefficient	$\leq 0.01\%$ of measurement range/°C
Type of connection	Tension clamp connection with actuator	Type of mounting	Frontpanel mounting, Front mounting
Voltage supply	21.6...253 VAC, (50...60 Hz) or 19.2...300 VDC		

Input

Input frequency	0.001...50 kHz	Min. pulse duration (reset input)	20 μ s...999.9 s
Number of inputs	1	Response time	≤ 1 Period + 100 ms
Sensor	S0 (trig-level low: ≤ 2.2 mA high: ≥ 9.0 mA), Special current (trig-level: user-defined), Special voltage (trig-level: user-defined), TTL (trig-level low: ≤ 0.8 V high: ≥ 2.0 V), Tacho (trig-level low: ≤ 50 mV high: $\geq +50$ mV), NAMUR sensor, according to EN60947-5-6, NPN / PNP transistor (trig-level low: ≤ 4 V high: ≥ 7 V), Trigger level adjustable, Switch	Sensor supply	5...17 V
Type	Adjustable frequencies		

ACT20D-LED-FI-AO-2RC-AC-DC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Output (digital)**

Alarm function	Over / under frequency, Overspeed / underspeed, Holding function can be activated	Contact material	Cu
Hysteresis	0...100 %	Max. switching frequency	15 Hz
Max. switching voltage, AC	250 V	Max. switching voltage, DC	30 V
Number of digital outputs	2	Rated switching current	2 A
Rated switching voltage	24 V AC ... 250 V AC	Status indicator	Green LED
Switch-off delay	0...3600 s	Switch-on delay	0...3600 s
Switching capacity	500 VA	Switching thresholds	Adjustable
Switching thresholds	All values in display range are configurable	Type	2 x 1 CO contact (hard gold-plated)
Type of switch function	direct or inverted		

Output (analogue)

Load resistance current	≤ 800 Ω	Number of analogue outputs	1
Output behaviour on failure downscale	3.5 mA	Output behaviour on failure upscale	23 mA
Output current	0...20 mA, 4...20 mA, 20... 0 mA, 20...4 mA	Signal output	direct or inverted
Type (analogue output)	'active','connected control must be passive'		

Insulation coordination

Galvanic isolation	between input / output / supply / relay	Insulation voltage	2.3 kVAC (Test) / 250 VAC (operating state)
Pollution severity	2	Surge voltage category	II

Connection data

Wire connection method	Clamping yoke, pluggable	Type of connection	Tension clamp connection with actuator
Wire connection cross section AWG, min.	AWG 30	Wire connection cross section AWG, max.	AWG 16
Wire connection cross section, finely stranded, min.	0.13 mm ²	Wire connection cross section, finely stranded, max.	2.8 mm ²

Classifications

ETIM 6.0	EC000677	ETIM 7.0	EC000677
ETIM 8.0	EC000677	ETIM 9.0	EC000677
ECLASS 9.0	27-14-31-10	ECLASS 9.1	27-21-03-01
ECLASS 10.0	27-14-31-10	ECLASS 11.0	27-14-31-10
ECLASS 12.0	27-14-31-10	ECLASS 13.0	27-14-31-10

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	f4905d12-f516-4eb5-90a8-8c87685bc956

ACT20D-LED-FI-AO-2RC-AC-DC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Con- [RCM certification](#)
formity [DNV certification](#)
[UL certification](#)
[Declaration of Conformity](#)

User Documentation [Instruction sheet](#)

Catalogues [Catalogues in PDF-format](#)



ACT20D-LED-FI-AO-2RC-AC-DC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings


Dimensioned drawing



Wiring diagram




Wiring diagram



Supply



part of the setting menu



ACT20D-LED-FI-AO-2RC-AC-DC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Process value indicators with LED display - ACT20D**

Devices in this series display universal analogue process values.

Depending on the version, the devices convert/isolate the signals into an analogue current signal and have additional limit value relays which switch further signals. Features:

- Several sensor variants can be processed.
- An auxiliary power supply is required.
- Even in unfavourable lighting conditions, the display value is clearly visible.

General ordering data

Type	PROTECTIVE COVER	Version
Order No.	2964330000	Display, Hood
GTIN (EAN)	4099986768086	
Qty.	1 pc(s).	