

PV PS VAPM 5P F**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Order No.	2920110000
Type	PV PS VAPM 5P F
GTIN (EAN)	4099986583009
Qty.	1 pc(s).

PV PS VAPM 5P F

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	149.5 g
------------	---------

Temperatures

Continuous operating temp., min.	-40 °C	Continuous operating temp., max.	105 °C
----------------------------------	--------	----------------------------------	--------

General Data

Colour	black	Conductor cross-section, max.	16 mm ²
Conductor cross-section, min.	0.2 mm ²	Insulation strength	≥ 1000 MΩ
Material	Polycarbonate	Number of poles	5
Pollution severity	3	Rated impulse voltage (DIN EN 61984)	6 kV
Type of connection	Screw connection		

Technical data

Conductor cross-section, max.	16 mm ²	Conductor cross-section, min.	0.2 mm ²
Pollution severity	3	Protection degree	IP65, in closed state, IP2x open
Rated current	60 A	Rated voltage	600 V

Guarantee

Time interval	2 years
---------------	---------

Classifications

ETIM 6.0	EC002928	ETIM 7.0	EC002928
ETIM 8.0	EC002928	ETIM 9.0	EC002928
ECLASS 9.0	22-57-92-03	ECLASS 9.1	27-44-01-07
ECLASS 10.0	27-44-01-07	ECLASS 11.0	22-57-02-92
ECLASS 12.0	22-57-02-92	ECLASS 13.0	22-57-02-92

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Product Change Notification	Änderung für PV – AC Steckverbinder Change to PV – AC connector
Catalogues	Catalogues in PDF-format

PV PS VAPM 5P F

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

