

VPU AC I O N-PE 305/50 LH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

In the event of a defective arrester, you can easily reorder this spare arrester, replace the defective arrester and thus restore protection.

General ordering data

Version	Surge protection
Order No.	2983630000
Type	VPU AC I O N-PE 305/50 LH
GTIN (EAN)	4099986839755
Qty.	1 pc(s).

VPU AC I O N-PE 305/50 LH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	105.7 mm	Height (inches)	4.161 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	50.8 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity at operating temperature	5 - 95% rel. humidity		

Probability of failure

MTBF	15 a
------	------

General data

Acoustic signal	No	Colour	orange, black, blue
Design	Installation housing, Insta IP 20	Operating altitude	≤ 4000 m
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20 in installed state
Rail	TS 35	UL 94 flammability rating	V-0
Version	Surge protection		

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	IV
--------------------	---	------------------------	----

Rated data IEC / EN

Acoustic signal	No	Discharge current I_{\max} (8/20μs) N-PE	100 kA
Discharge current I_n (8/20μs) N-PE	50 kA	Energy coordination (≤10 m)	Type I, Type II, Type III
Frequency range, max.	60 Hz	Frequency range, min.	50 Hz
Fuse	Not required	Mains voltage	230 V / 400 V
Max. continuous voltage, U_c (AC)	300 V	Number of poles	1
Protection level U_p at I_n (N-PE)	≤ 1500 V	Protection level, U_p wire - PE	1,500 V
Protection level, U_p wire - wire	1,500 V	Rated voltage (AC)	240 V
Requirements category acc. to IEC 61643-11	Type I, Type II	Requirements class, acc. to EN 61643-11	T1, T2
Short-circuit current rating I_{SCCR}	50 kA	Standards	IEC61643-11, EN61643-11
Temporary surge voltage (over-voltage) - TOV	442 V	Voltage type	AC

Connection data

Type of connection	Plug-in connection	Wire cross-section, solid, max.	35 mm ²
--------------------	--------------------	---------------------------------	--------------------

Guarantee

Time interval	5 years
---------------	---------

VPU AC I O N-PE 305/50 LH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	CAD data – STEP
User Documentation	Beipackzettel / Instruction sheet
Catalogues	Catalogues in PDF-format