

**CH-W-S-A11-P10-V****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Smart charging solutions for individual challenges - The intelligent and networkable EV charging box family AC SMART. Ready for any application scenario in the private and commercial sector: from simple charging with a single charging point through integration into smart grids to the complex management of entire charging parks.

The three platform-based feature lines ECO, VALUE and ADVANCED cover the most common use-cases and can be adapted to individual applications by means of standardized interfaces and versatile configuration options. Clever features, such as RFID- or mobile app-based user authentication, adjustability of the charging current, integrated load and charge management or self-sufficient PV surplus charging, make the AC SMART Boxes a flexible, customizable and in addition to that, an efficient and sustainable charging solution.

**General ordering data**

Version	Wallbox, With attached 10 m cable and type 2 plug, Mobile App, RFID/NFC
Order No.	<a href="#">2911250000</a>
Type	CH-W-S-A11-P10-V
GTIN (EAN)	4099986532229
Qty.	1 pc(s).

**CH-W-S-A11-P10-V****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	149 mm	Depth (inches)	5.866 inch
Height	439 mm	Height (inches)	17.283 inch
Width	273 mm	Width (inches)	10.748 inch
Net weight	6,400 g		

**Temperatures**

Storage temperature	-40 °C...70 °C	Operating temperature	-30 °C...50 °C
---------------------	----------------	-----------------------	----------------

**System requirements**

Connection system	With attached 10 m cable and type 2 plug	Type of communication to vehicle	Control Pilot (CP), Proximity Pilot / Plug Present (PP)
Charge mode	Mode 3	Protection class	I
Surge voltage category	III	Pollution severity	3

**Material data**

Max. relative humidity during storage	95 %	Operating temperature, max.	50 °C
Operating temperature, min.	-30 °C	Storage temperature, max.	70 °C
Storage temperature, min.	-40 °C		

**Performance specification**

Performance specification	Input voltage type	AC
	Input voltage	400 V
	Input current, max.	16 A
	Charging power, max	11 kW
	Adjustment accuracy	1 A
	Charging current adjustable	Yes
	Charging current, min	6 A

**Features**

Charging data exportable	Yes	Protection degree	IP54
Type of status indicator	RGB LED	Welding detection	Yes
Failure shutdown	Yes	Failure shutdown method	All-pole
DC - residual current detection integrated	Yes	DC - residual current	6 mA
Type of residual current detection to be provided by the installation	RCD Type A	User authentication	Yes
Mobile App available	Yes	User authentication type	Mobile App, RFID/NFC
Energy measurement integrated	Yes	Integrated energy measuring MID conform	Yes
Load management integrated	Yes	Load management type	static
Communication integrated	Yes	Supported protocols	Modbus RTU, Modbus TCP, OCPP 1.6 (J)

**Interfaces**

Wifi frequency	2,4 GHz	Wi-Fi Standard	802.11 b/g/n
Bluetooth module	Bluetooth Low Energy	Ethernet ports	2
Digital inputs	5 (12 V / 6 mA)	Digital outputs	1 (12 V / 100 mA)
Type of protocol of serial interface	RS485		

**CH-W-S-A11-P10-V****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Assembly**

Installation	Wall mounting, Stand Mounting
--------------	-------------------------------

**Included in delivery**

Included in delivery	Drilling template, Instruction sheet, 5 RFID-transponder, Mounting screws, Assembly dowels, cover
----------------------	---

**Housing**

Operating altitude	≤ 3000 m	Housing main material	PC
Protection degree	IP54	Colour	black, Anthracite, grey
Impact resistance	IK10 in accordance with IEC 62262		

**Approvals and norms**

Approvals	IEC 61851-1, IEC 61851-21-2, IEC 62196-1, IEC 62196-2, EN 50620, EN 301 489-1, EN 301 908-1, EN 301 511, EN 300 328, EN 300 330 v.2.1.1, EN 62368-1, EN 55011
-----------	---

**Connection data (supply cable)**

Conductor cross-section, max.	16 mm <sup>2</sup>
-------------------------------	--------------------

**Classifications**

ETIM 6.0	EC002883	ETIM 7.0	EC002883
ETIM 8.0	EC002883	ETIM 9.0	EC002883
ECLASS 9.0	27-14-47-01	ECLASS 9.1	27-14-47-01
ECLASS 10.0	27-14-47-01	ECLASS 11.0	27-14-47-01
ECLASS 12.0	27-14-47-01	ECLASS 13.0	27-14-47-01

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	dde0af7d-c609-4edf-88f1-0eb427589c0f

**Approvals**

Approvals



## CH-W-S-A11-P10-V

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">CE declaration</a> <a href="#">Warranty Weidmüller e-mobility products</a> <a href="#">Gewährleistung Weidmüller e-mobility Produkte</a> <a href="#">Self declaration test certificates AC SMART</a> <a href="#">Selbsterklärung Testzertifikate AC SMART</a>
Engineering Data	<a href="#">Installationsvideo AC SMART</a> <a href="#">Installation Video AC SMART</a> <a href="#">AC SMART Modbus registers</a> <a href="#">Application notes – Use of an external Modbus TCP/RTU tag list (DE, EN)</a> <a href="#">Application notes – PV-surplus charging AC SMART (DE, EN)</a> <a href="#">Application notes – Integration of the AC SMART into an external load management (DE, EN)</a>
Software	<a href="#">Firmware – Current Bluetooth Firmware AC SMART</a> <a href="#">Firmware – Current Firmware AC SMART</a> <a href="#">Firmware – Current WiFi Firmware AC SMART</a> <a href="#">Firmware – Archive Firmware files AC SMART</a> <a href="#">Firmware – Release notes Current firmware AC SMART</a> <a href="#">Firmware – Combined Firmware Package AC SMART</a>
Technical Documentation	<a href="#">Abnahmeprotokoll AC SMART</a>
Tender specification	<a href="#">Ausschreibungstexte</a> <a href="#">Tender texts</a>
User Documentation	<a href="#">Broschüre Wallbox AC SMART, AC Ladekabel, Basiskomponenten</a> <a href="#">Brochure EV charging box AC SMART, AC charging cables, Basic components</a> <a href="#">Instructionsheet AC SMART</a> <a href="#">MANUAL AC SMART (DE)</a> <a href="#">MANUAL AC SMART (EN)</a> <a href="#">MANUAL AC SMART (FR)</a> <a href="#">MANUAL AC SMART (IT)</a> <a href="#">MANUAL AC SMART (ES)</a> <a href="#">MANUAL AC SMART (NL)</a> <a href="#">MANUAL AC SMART (NO)</a> <a href="#">MANUAL AC SMART (SV)</a> <a href="#">MANUAL AC SMART (CS)</a> <a href="#">MANUAL AC SMART (HU)</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**CH-W-S-A11-P10-V**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**CH-W-S-A11-P10-V****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****AC Boxes****General ordering data**

Type	PVC AC 1I 1O SPD2R + RJ ...	Version
Order No.	<a href="#">8000104168</a>	AC voltage version, Auxiliary and alarm contact, TN-C-S, TN-S, IT with
GTIN (EAN)	4099986573475	N, IT without N, TT
Qty.	1 pc(s).	

**Design-Cover**

Design-Cover for AC SMART in white and black.

**General ordering data**

Type	EQ-W-S-C2-D-WH
Order No.	<a href="#">2922620000</a>
GTIN (EAN)	4099986617865
Qty.	1 pc(s).

Type	EQ-W-S-C2-D-BK
Order No.	<a href="#">2958080000</a>
GTIN (EAN)	4099986745766
Qty.	1 pc(s).

**CH-W-S-A11-P10-V****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Stands**

Whether carport, driveway, front garden, customer, or employee parking lot: With the easy to assemble Weidmüller stand, you are flexible in your choice of installation location. Thanks to its compact and timeless design, the Weidmüller stand fits into any architectural environment. The housing surfaces offer space for individualization – for example with logos or company names. Premium components and materials, certified production in Germany, as well as the durable design with ease of installation, underline the sustainable concept of the charging solution.

**General ordering data**

Type	ST-W-S-SINGLE
Order No.	<a href="#">2904100000</a>
GTIN (EAN)	4099986531321
Qty.	1 pc(s).
Type	ST-W-S-DOUBLE
Order No.	<a href="#">2915210000</a>
GTIN (EAN)	4099986543478
Qty.	1 pc(s).
Type	ST-W-S-BLANK
Order No.	<a href="#">2904120000</a>
GTIN (EAN)	4099986531581
Qty.	1 pc(s).