

FUSE WSFL 10X85 20A 1K5V GPV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



gPV 10×85 cylindrical fuse cartridges are designed to provide compact, safe and economical protection of photovoltaic modules (field protection) with voltages up to 1,500 DC. They provide protection against both overload and short circuit (gPV class according to the requirements of IEC60269-6 and UL248-19 standards).

Informations générales de commande

Version	Photovoltaïque, Fusible, 1500 V, 10x85, gPV, 20 A
Référence	4000002610
Type	FUSE WSFL 10X85 20A 1K5V GPV
GTIN (EAN)	8430243419635
Qté.	50 pièce(s)

FUSE WSFL 10X85 20A 1K5V GPV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Caractéristiques techniques****Dimensions et poids**

Hauteur	85 mm	Hauteur (pouces)	3,346 inch
Largeur	10,3 mm	Largeur (pouces)	0,406 inch
Poids net	1,94 g		

Classifications

ETIM 7.0	EC002704	ETIM 8.0	EC002704
ETIM 9.0	EC002704	ECLASS 11.0	27-14-20-02
ECLASS 12.0	27-14-20-02	ECLASS 13.0	27-14-20-02

Élément fusible

Conducteur fusible standard	IEC 60269-6	Courant	20 A
Tension nominale DC	1 500 V		

Agréments

ROHS	Conforme
------	----------

Téléchargements

Données techniques	CAD data – Advanced Datasheet
Catalogue	Catalogues in PDF-format