

H0,25/7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.comFor conductors from 0.25 to 6,0 mm² (AWG 24 - 10)

tin-plated copper

dimensional tolerances to DIN 46228 part 1

- supplied loose in polybag

General ordering data

| | |
|------------|--|
| Version | Wire-end ferrule, Standard, 7 mm, 7 mm |
| Order No. | 2919620000 |
| Type | H0,25/7 |
| GTIN (EAN) | 4099986576742 |
| Qty. | 1,000 pc(s). |
| Packaging | loose |

H0,25/7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|----------|--------|-----------------|------------|
| Height | 7 mm | Height (inches) | 0.276 inch |
| Diameter | 1.7 mm | Net weight | 0.03 g |

Technical data

| | | | |
|------------------------|---------------------|---------|----------|
| Description of article | (2)Wire-end ferrule | Version | Standard |
|------------------------|---------------------|---------|----------|

Wire-end ferrules

| | | | |
|---|---------|-----------------------------|----------------------|
| Collar diameter (D2) | 1.7 mm | Conductor cross-section | 0.25 mm ² |
| Contact surface diameter (D1) | 0.75 mm | Contact surface length (L2) | 7 mm |
| L1 in mm | 7 mm | Stripping length | 7 mm |
| Wire connection cross section AWG, max. | AWG 24 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000005 | ETIM 7.0 | EC000005 |
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ECLASS 9.0 | 27-40-02-01 | ECLASS 9.1 | 27-40-02-01 |
| ECLASS 10.0 | 27-40-02-01 | ECLASS 11.0 | 27-40-02-01 |
| ECLASS 12.0 | 27-40-02-01 | ECLASS 13.0 | 27-40-02-01 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|

H0,25/7

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

