

VPU AC I 3+1 255/12.5 LCF MB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Type I + II lightning and surge protection**

- High discharge current I_{imp} with 12.5 kA (10/350 μ s)
- Low protection level Up of 1.5 kV
- Suitable for protection classes III and IV (LPL III/IV)
- Leakage current free series for use in front of the electrical meter
- Tested in accordance with IEC 61643-11
- Variants with and without remote monitoring function

General ordering data

Version	low voltage, Surge protection, Surge protection I / II, TN-S, TT
Order No.	2976620000
Type	VPU AC I 3+1 255/12.5 LCF MB
GTIN (EAN)	4099986825895
Qty.	1 pc(s).

VPU AC I 3+1 255/12.5 LCF MB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	65 mm	Depth (inches)	2.559 inch
Height	105 mm	Height (inches)	4.134 inch
Width	72 mm	Width (inches)	2.835 inch
Net weight	430 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity at operating temperature	5 - 95% rel. humidity		

General data

Colour	black	Design	Installation housing; 4TE, Insta IP 20
Operating altitude	≤ 4000 m	Optical function display	green = OK; red = arrester is defective - replace
Protection degree	IP20 in installed state	Rail	TS 35
Segment	Power distribution	UL 94 flammability rating	V-0
Version	low voltage, Surge protection, Surge protection I / II		

Insulation coordination acc. to EN 50178

Surge voltage category	I, III
------------------------	--------

Rated data IEC / EN

Discharge current I_{\max} (8/20μs) N-PE	100 kA	Discharge current I_{\max} (8/20μs) wire-PE	50 kA
Discharge current I_n (8/20μs) N-PE	50 kA	Discharge current I_n (8/20μs) wire-PE	20 kA
Discharge current, max. (8/20 μs)	50 kA	Energy coordination (≤10 m)	Type I, Type II, Type III
Follow-on current extinguishing capability I_{fi}	25 kA	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Fuse	No Fuse necessary ≤250 A gG
Leakage current at U_n	0 μA	Lightning test current I_{imp} (10/350 μs) (L-PE)	12.5 kA
Lightning test current, I_{imp} (10/350 μs) (N-PE)	50 kA	Low voltage network	TN-S, TT
Max. continuous voltage, U_c (AC)	255 V	Number of poles	4
Protection level U_p at I_N (L/N-PE)	≤ 1500 V	Protection level U_p at I_N (N-PE)	≤ 1500 V
Rated voltage (AC)	240 V	Requirements category acc. to IEC 61643-11	Type I, Type II
Requirements class, acc. to EN 61643-11	T1, T2	Response time	<100 ns
Short-circuit current rating I_{SCCR}	25 kA	Standards	IEC 61643-11, EN 61643-11
Temporary surge voltage (over-voltage) - TOV	442 V	Voltage type	AC

VPU AC I 3+1 255/12.5 LCF MB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Connection data

Stripping length	18 mm	Wire connection method	Screw connection
Type of connection	Screw connection	Tightening torque, min.	2 Nm
Tightening torque, max.	4.5 Nm	Clamping range, min.	4 mm ²
Clamping range, max.	35 mm ²	Wire cross-section, solid, min.	1.5 mm ²
Wire cross-section, solid, max.	35 mm ²	Wire connection cross section, finely stranded, min.	1.5 mm ²
Wire connection cross section, finely stranded, max.	35 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	25 mm ²
Connection cross-section, stranded, min.	1.5 mm ²	Connection cross-section, stranded, max.	35 mm ²

Guarantee

Time interval	5 years
---------------	---------

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

Approvals

Approvals



ROHS	Conform
------	---------

Downloads


Approval/Certificate/Document of Conformity	EU Konformitätserklärung / EU Declaration of Conformity
Engineering Data	CAD data – STEP
User Documentation	Beipackzettel / Instruction sheet
Catalogues	Catalogues in PDF-format

VPU AC I 3+1 255/12.5 LCF MB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



VPU AC I 3+1 255/12.5 LCF MB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Crosshead screwdriver Phillips**

VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

General ordering data

Type	SDIK PH1 X 80	Version
Order No.	2749890000	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1
GTIN (EAN)	4050118897098	
Qty.	1 pc(s).	

Slotted screwdriver

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Type	SDIS 1.0X5.5X125	Version
Order No.	2749850000	Screwdriver, Blade width (B): 5.5 mm, Blade length: 125 mm, Blade
GTIN (EAN)	4050118897050	thickness (A): 1 mm
Qty.	1 pc(s).	

VPU AC I 3+1 255/12.5 LCF MB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Blank**

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ESG 6/15 K MC NE WS	Version
Order No.	1880100000	ESG, Device markers x 15 mm, PA 66, Colour: white, Self-adhesive
GTIN (EAN)	4032248478781	
Qty.	200 pc(s).	