

**EPAK-VMR-3PH-480-ILP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The analogue converters of the EPAK series are characterised by their compact design.

The wide range of functions available with this series of analogue converters make them suitable for applications which do not require international approvals.

Properties:

- Safe isolation, conversion and monitoring of your analogue signals
- Configuration of the input and output parameters directly on the device via DIP switches
- No international approvals
- High interference resistance

**General ordering data**

Order No.	<a href="#">7760054301</a>
Type	EPAK-VMR-3PH-480-ILP
GTIN (EAN)	6944 169747700
Qty.	1 pc(s).

## EPAK-VMR-3PH-480-ILP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	89 mm	Depth (inches)	3.504 inch
Height	100 mm	Height (inches)	3.937 inch
Width	17.5 mm	Width (inches)	0.689 inch
Length	100 mm	Length (inches)	3.937 inch
Net weight	80 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-20 °C...60 °C
Humidity at operating temperature	0...95 % (no condensation)		

## Probability of failure

SIL in compliance with IEC 61508	None
----------------------------------	------

## Input

Input frequency	40...60 Hz	Input measurement range	165...550 V AC
Number of inputs	1 x three-phase (R, S, T, N)		

## Output

Number of outputs	1
-------------------	---

## Output (digital)

Alarm function	Phase error, Phase sequence, Asymmetry, Window alarm: -15% for min. value (fixed), 10% for max. value (fixed), Hysteresis: 10 V	Max. switching frequency	20 Hz
Max. switching voltage, AC	250 V	Max. switching voltage, DC	30 V
Number of digital outputs	1	Rated switching current	3 A
Type	Relay, 1 CO contact		

## General data

Accuracy	5 % of FSR	Configuration	none
Galvanic isolation	between input/output, yes, between input/output/supply	Step response time	≤ 200 ms (10...90%)
Temperature coefficient	≤ 250 ppm/K of measuring range, ± 250 ppm/K, 350 ppm/K	Voltage supply	from the measuring circuit

## Insulation coordination

EMC standards	IEC 61000-6-2, IEC 61000-6-4	Galvanic isolation	between input/output, yes, between input/output/supply
Impulse withstand voltage	4 kV (1.2/50 µs)	Insulation voltage	2.2 kVAC, 1 min, 50 Hz
Pollution severity	2	Rated voltage	300 V
Surge voltage category	II		

## EPAK-VMR-3PH-480-ILP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Connection data

Type of connection	Screw connection	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	2 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping range, max.	2 mm <sup>2</sup>
Wire connection cross section AWG, min.	AWG 30	Wire connection cross section AWG, max.	AWG 14

## Classifications

ETIM 6.0	EC002654	ETIM 7.0	EC002654
ETIM 8.0	EC002654	ETIM 9.0	EC002654
ECLASS 9.0	27-21-01-22	ECLASS 9.1	27-21-01-22
ECLASS 10.0	27-21-01-22	ECLASS 11.0	27-21-01-22
ECLASS 12.0	27-21-01-22	ECLASS 13.0	27-21-01-22

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6a722fc5-2d22-41b4-9544-5b95e45a4b77

## Approvals

Approvals



ROHS Conform

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Instruction sheet</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## EPAK-VMR-3PH-480-ILP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

