

HDC 16B TOBU 1M25G EXI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The option of disconnecting cables in the EXI area simplifies installation and servicing and enables better preparation.

The Rockstar® EXI enclosures shown here are identified for use by their article designation.

A blue color is therefore not required. A blue EXI gland is required to complete the enclosure.

General ordering data

Version	, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 25
Order No.	3001440000
Type	HDC 16B TOBU 1M25G EXI
GTIN (EAN)	4099986902473
Qty.	1 pc(s).

HDC 16B TOBU 1M25G EXI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	93.3 mm	Depth (inches)	3.673 inch
Height	61 mm	Height (inches)	2.402 inch
Width	57.8 mm	Width (inches)	2.276 inch
Net weight	224 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Dimensions

Cable entry	w. thread	Height of housing B	61 mm
Total length housing	93.03 mm	Width housing C	43 mm

General data

EMC housings	No	Housing main material	diecast aluminium
Material of locking element	Stainless steel, rust-proof	Protection degree	IP65 (in plugged condition)
Surface finish	Powder coating	Tightening torque	1.2 Nm
Explosion protection type	II 2G Ex ib IIC T6 Gb		

Version

BG	6	Cable entry	w. thread
Clamp version	Side-locking clamp	Colour (RAL)	RAL 7035
Design	Standard	Design of housing	Cable entry from side, Plug housing
Design of locking system	Side-locking clamp on lower side	Internal thread	M 25
Number of cable entry on top	1	Size	6
Size of cable entries	M 25	Suitable for ModuPlug®	Yes
Tightening torque	1.2 Nm	Top part/bottom part/lid	upper part
Type	Plug		

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ETIM 9.0	EC000437
ECLASS 9.0	27-44-02-02	ECLASS 9.1	27-44-02-02
ECLASS 10.0	27-44-02-02	ECLASS 11.0	27-44-02-02
ECLASS 12.0	27-44-02-02	ECLASS 13.0	27-44-02-02

Downloads

Catalogues	Catalogues in PDF-format
------------	--

HDC 16B TOBU 1M25G EXI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Chloroprene seal material, -40°C - +70°C**

Polyamide cable glands, which are suitable for usage in explosion risk zones Ex e (increased safety) and Ex i (intrinsic safety).

Weidmüller offers a product family without restrictions and besides compliance with standards, the cable gland excels thanks to its increased impact resistance of 4/7 Joule and a possible temperature range down to -60°C without restrictions. They have been tested to the current standard and EN 60079-0 directive, they are ATEX and IECEx certified.

General ordering data

Type	VG M25 EXI 14-18 CR7J G4	Version
Order No.	2722280000	VG Exi 7J (Ex plastic cable gland 7J Exi), Cable glands, straight, M 25,
GTIN (EAN)	4050118821512	10 mm, OD min. 14 - OD max. 18 mm, IP54, IP66, IP67, IP68 - 5 bar
Qty.	25 pc(s).	(30 min.), Polyamide 6
Type	VG M25 EXI 12-17 CR7J G4	Version
Order No.	2722270000	VG Exi 7J (Ex plastic cable gland 7J Exi), Cable glands, straight, M 25,
GTIN (EAN)	4050118821505	10 mm, OD min. 12 - OD max. 17 mm, IP54, IP66, IP67, IP68 - 5 bar
Qty.	50 pc(s).	(30 min.), Polyamide 6