

**EPAK-CI-4CO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The analogue converters of the EPAK series are characterised by their compact design.

The wide range of functions available with this series of analogue converters make them suitable for applications which do not require international approvals.

Properties:

- Safe isolation, conversion and monitoring of your analogue signals
- Configuration of the input and output parameters directly on the device via DIP switches
- No international approvals
- High interference resistance

**General ordering data**

Order No.	<a href="#">7760054308</a>
Type	EPAK-CI-4CO
GTIN (EAN)	6944 169747748
Qty.	1 pc(s).

## EPAK-CI-4CO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	89 mm	Depth (inches)	3.504 inch
Height	100 mm	Height (inches)	3.937 inch
Width	17.5 mm	Width (inches)	0.689 inch
Net weight	80 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-20 °C...60 °C
---------------------	----------------	-----------------------	----------------

## Probability of failure

SIL in compliance with IEC 61508	None
----------------------------------	------

## Input

Input current	0...20 mA, 4...20 mA	Input resistance, current	≤ 100 Ω
Number of inputs	1		

## Output

Load impedance current	≤ 300 Ω	Number of outputs	4
Output current	0...20 mA, 4...20 mA		

## Output (digital)

Max. switching voltage, AC	0 V	Rated switching current	0.1 A
----------------------------	-----	-------------------------	-------

## Output (analogue)

Output current	0...20 mA, 4...20 mA
----------------	----------------------

## General data

Accuracy	0.1% FSR	Configuration	none
Galvanic isolation	between input/output/supply	Power consumption	≤ 1.9 W
Step response time	≤ 500 ms	Temperature coefficient	≤ 300 ppm/K
Voltage supply	20...35 V DC		

## Insulation coordination

EMC standards	IEC 61326-1	Galvanic isolation	between input/output/supply
Impulse withstand voltage	3 kV (1.2/50μs)	Insulation voltage	1.5 kV <sub>eff</sub>
Pollution severity	2	Rated voltage	300 V
Surge voltage category	II		

## Connection data

Type of connection	Screw connection	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	2 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping range, max.	2 mm <sup>2</sup>
Wire connection cross section AWG, min.	AWG 30	Wire connection cross section AWG, max.	AWG 14

## EPAK-CI-4CO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Classifications

ETIM 6.0	EC002653	ETIM 7.0	EC002653
ETIM 8.0	EC002653	ETIM 9.0	EC002653
ECLASS 9.0	27-21-01-20	ECLASS 9.1	27-21-01-20
ECLASS 10.0	27-21-01-20	ECLASS 11.0	27-21-01-20
ECLASS 12.0	27-21-01-20	ECLASS 13.0	27-21-01-20

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6a722fc5-2d22-41b4-9544-5b95e45a4b77

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Instruction sheet</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## EPAK-CI-4CO

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

