

SKH2 F32 (Z+B) LPP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



Plug-in card holders are used to adapt cards from the Euro format (19") to connectors in compliance with IEC 603/ DIN 41612 and DIN 41617.

Plug-in card holders consist of the following components:

- Circuit board with standard connectors and inserts with clamping-yoke connection.
- Flange housing and holder/pull-out mechanism for the circuit card.
- Plug-in card and mounting foot for attaching to mounting rail or directly to panel.

The plug-in card holders are normally used in the following cases:

- For quick adaptation in industrial applications of different 19" modules, and for avoiding the expense of a 19" rack.
- When there are only a few cards to install and connect.
- The circuit board is located in a remote position where the cabling cannot be easily handled.
- An older system needs to be updated with additional electronics modules.
- For test devices, production processes and laboratories: where circuit boards need to be swapped out quickly and connections must be easy to handle.

General ordering data

Version	Interface, Plug-in connector, acc. to DIN 41612 female, 32F
Order No.	8174850000
Type	SKH2 F32 (Z+B) LPP
GTIN (EAN)	4008190169343
Qty.	1 pc(s).

SKH2 F32 (Z+B) LPP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	193 mm	Depth (inches)	7.598 inch
Height	81 mm	Height (inches)	3.189 inch
Width	160 mm	Width (inches)	6.299 inch
Net weight	381 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	0...55 °C
---------------------	-------------	-----------------------	-----------

Connection data

Connection (field side)	LP 5.08mm	Connection on control side	Plug-in connector, acc. to DIN 41612 female
Contact assembly	z and b	Design of the pluggable board	100x160 mm euro format for 19" racks
Number of poles (control side)	32-pole female	Type (control side)	32F

Rating data

Rated voltage	250 V UC	Rated current per connection	4 A
---------------	----------	------------------------------	-----

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	250 V
Surge voltage category	II	Pollution severity level	2
Pulse voltage test (1,2/50µs)	2.1 kV	Insulation test voltage AC	1.2 kV

Connection field

Clamping range, max.	6 mm ²	Clamping range, min.	0.5 mm ²
Flexible with sleeve, max.	2.5 mm ²	Flexible with sleeve, min.	0.5 mm ²
Flexible, max. H05(07) V-K	4 mm ²	Flexible, min. H05(07) V-K	0.5 mm ²
Max. wire cross-section, AWG	AWG 12	Min. wire cross-section, AWG	AWG 26
Sleeve with plastic collar, max.	2.5 mm ²	Solid, max. H05(07) V-U	6 mm ²
Solid, min. H05(07) V-U	0.5 mm ²	Stripping length	6 mm
Tightening torque, max.	0.6 Nm	Tightening torque, min.	0.5 Nm
Type of connection	Screw connection		

Classifications

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ETIM 9.0	EC002780
ECLASS 9.0	27-14-11-52	ECLASS 9.1	27-24-22-92
ECLASS 10.0	27-14-11-52	ECLASS 11.0	27-14-11-52
ECLASS 12.0	27-14-11-52	ECLASS 13.0	27-14-11-52

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

SKH2 F32 (Z+B) LPP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity

[Declaration of Conformity](#)

Product Change Notification

[20211110 Technical change to SKH interfaces!](#)

Catalogues


[Catalogues in PDF-format](#)

SKH2 F32 (Z+B) LPP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



SKH2 F32 (Z+B) LPP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Steel**

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Type	TS 35X15/2.3 2M/ST/ZN	Version
Order No.	0498000000	Terminal rail, without slot, Accessories, 35 x 15 x 2000 mm, Steel,
GTIN (EAN)	4008190042493	galvanic zinc plated and passivated
Qty.	2 m	
Type	TS 35X7.5 2M/ST/ZN	Version
Order No.	0383400000	Terminal rail, without slot, Accessories, 35 x 7.5 x 2000 mm, Steel,
GTIN (EAN)	4008190088026	galvanic zinc plated and passivated
Qty.	2 m	