


DK NOR 35 24VDC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Logic functions AND, NAND, OR and NOR in modular terminal format with a rated cross-section of 4 mm². They each have five inputs which are fed – with logic gating – via a 24 V/20 mA PNP output. The logic components can be used for many applications involving the coupling of digital sensor/actuator signals with automation devices.

General ordering data

Version	Function component, NOR Gate
Order No.	8248330000
Type	DK NOR 35 24VDC
GTIN (EAN)	4008190406714
Qty.	5 pc(s).

DK NOR 35 24VDC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	57 mm	Height (inches)	2.244 inch
Width	12 mm	Width (inches)	0.472 inch
Length	65 mm	Length (inches)	2.559 inch
Net weight	29 g		

Temperatures

Storage temperature	-40 °C...60 °C	Operating temperature	0 °C...50 °C
Humidity	40 °C / 93 % rel. humidity, no condensation		

General data

Current consumption	<5 mA	Galvanic isolation	Without isolation
Humidity	40 °C / 93 % rel. humidity, no condensation	Input/Output	Logic module
Open sides	right	Rail	TS 35
Type of connection	Screw connection	Voltage supply	24...30 V DC

Insulation coordination

Standards	EN 61000-6-2:2005, EN 61000-6-3:2007/ A1:2011, EN 61000-6-4:2007 + A1:2011
-----------	--

Input

Input current	Approx. 1.5 mA per input (24 V)	Number of inputs	5
Pulse duration	≥ 50 µs	Rated input level	24 V DC= High, 0 V = Low
Rated voltage	Max. 30 V		

Output

Load impedance current	≤ 600 Ω	Number of outputs	1
Output current	max. 20 mA	Output level	PNP, Ub-1.8 V
Switching thresholds	High <15 V, low <9 V		

Connection data

Type of connection	Screw connection	Clamping range, rated connection	4 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	4 mm ²

Classifications

ETIM 6.0	EC001417	ETIM 7.0	EC001417
ETIM 8.0	EC001417	ETIM 9.0	EC001417
ECLASS 9.0	27-24-22-16	ECLASS 9.1	27-21-92-90
ECLASS 10.0	27-24-22-16	ECLASS 11.0	27-24-22-16
ECLASS 12.0	27-24-22-16	ECLASS 13.0	27-24-22-16

DK NOR 35 24VDC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	35d83707-6a3b-45b5-b9f8-6ba8184c863e

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Application notes – Declaration of Conformity
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

DK NOR 35 24VDC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

