

**FBCON SS CG 8WAY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

For standard industrial applications (non-hazardous areas), PROFIBUS PA junction boxes and limiters are available as 1-way, 2-way, 4-way, and 8-way distributors. FBCon limiters are designed to protect connected field devices from over voltages and short circuits. As voltage-limiting protective elements, suppressor diodes are used. Due to the integrated current limitation, the segment is also protected against short circuit on a spur line. EMC cable glands, protection class IP66 and a wide operating temperature range safely protect your connections in harsh environments.

**Functionality**

- EMC cable glands for trunk and spurs
- M12 connector for spurs
- External earthing stud
- Pressure equalizing element
- Protection class IP66
- Aluminium and stainless-steel versions
- Profibus PA / Foundation Fieldbus compatible

Note: The use of FBCon products with aluminum enclosures and / or M12 connectors is not recommended in strongly saline environments.

**General ordering data**

Version	Standard distributor, 8-way distributor, IP66
Order No.	<a href="#">8703470000</a>
Type	FBCON SS CG 8WAY
GTIN (EAN)	4032248398362
Qty.	1 pc(s).

## FBCON SS CG 8WAY

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	58 mm	Height (inches)	2.283 inch
Width	80 mm	Width (inches)	3.15 inch
Length	175 mm	Length (inches)	6.89 inch
Net weight	1,244 g		

## Temperatures

Storage temperature	-40 °C...80 °C	Ambient temperature	-40 °C...75 °C
Operating temperature	-40 °C...75 °C		

## Technical data

Bus system	Profibus-PA, Foundation Fieldbus	Cable glands	Stainless steel cable gland
Connection type PE	Spur line with cable gland	Design of housing	With pressure compensation element
Housing main material	Stainless steel, rust-proof, Aluminum	Housing surface	polished
Operating voltage	10 ... 31 V DC	Operating voltage $U_{max}$ , max.	32 V
Pollution severity	3	Protection degree	IP66
Type of distribution	8-way distributor	Type of mounting	surface-mounted

## Classifications

ETIM 6.0	EC001604	ETIM 7.0	EC001604
ETIM 8.0	EC001604	ETIM 9.0	EC001604
ECLASS 9.0	27-24-26-08	ECLASS 9.1	27-24-26-08
ECLASS 10.0	27-24-26-08	ECLASS 11.0	27-24-26-08
ECLASS 12.0	27-44-01-11	ECLASS 13.0	27-44-01-11

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	3a5f5913-76fc-4ff5-8563-4463f80bbe02

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

## Downloads

Product Change Notification	<a href="#">20220208 Technical change to FBCon field distributors (passive, with stainless steel housings)</a>
Software	<a href="#">WI-Segment-Calculator</a>
User Documentation	<a href="#">Application-Guide-Planning and installing Fieldbus networks-using-FBCon_english_deutsch</a> <a href="#">FBCon Segment Calculator_english</a> <a href="#">Instruction sheet</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

Creation date May 28, 2024 12:44:42 PM CEST

Catalogue status 18.05.2024 / We reserve the right to make technical changes.

## FBCON SS CG 8WAY

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

