

PAS CMR 0,5...2,5 A DC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image, Similar to illustration**

The PLUGCONTROL PAS CMRs present a simple, cost-effective solution for monitoring DC currents up to 10 A.

The monitoring relay (REED contact) comes attached to a standard base so that it can be mounted on a TS35 DIN rail.

Current monitoring of valves, servo-controls and DC motors are typical applications for these modules.

General ordering data

Version	Current monitoring, 0.5...2.5 A DC, Screw connection
Order No.	8742610000
Type	PAS CMR 0,5...2,5 A DC
GTIN (EAN)	4032248413928
Qty.	10 pc(s).

PAS CMR 0,5...2,5 A DC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	95 mm	Depth (inches)	3.74 inch
Width	15.3 mm	Width (inches)	0.602 inch
Length	92 mm	Length (inches)	3.622 inch
Net weight	69.6 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-20 °C...60 °C
Humidity at operating temperature	0...95 % (no condensation)	Humidity	5-95% relative humidity, T _u = 40°C, without condensation

Probability of failure

SIL in compliance with IEC 61508	None
----------------------------------	------

General data

Configuration	none	Galvanic isolation	2-way isolator, between input/output/supply
Rail	TS 35	Temperature coefficient	350 ppm/K

Insulation coordination

EMC standards	EN 55011, EN 61000-6-1, 2, 3, 4	Galvanic isolation	2-way isolator, between input/output/supply
Impulse withstand voltage	6 kV	Insulation voltage	4 kV _{eff} / 1 min.
Pollution severity	2	Rated voltage	300 V
Surge voltage category	III		

Input

Input current	0.5...2.5 A DC	Input resistance, current	<50 mΩ
Making current threshold	≤ 500 mA	Max. current	7.5 A for 10 s
Pulse duration	min. 1 ms	Secure off	≤ 50 mA

Output

Contact assembly	1 NO contact	Contact material	RH/Rd (Reed contact)*
Continuous current	100 mA	Max. switching frequency	20 Hz
Max. switching voltage, AC	250 V	Max. switching voltage, DC	100 V
Switching current	100 mA	Switching voltage AC, min.	1 V
Switching voltage DC, min.	1 V	Temperature coefficient	350 ppm/K

Connection data

Type of connection	Screw connection	Clamping range, rated connection	1.5 mm ²
Clamping range, min.	2.5 mm ²	Clamping range, max.	2.5 mm ²

PAS CMR 0,5...2,5 A DC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC002654	ETIM 7.0	EC002654
ETIM 8.0	EC002654	ETIM 9.0	EC002654
ECLASS 9.0	27-21-01-22	ECLASS 9.1	27-21-01-22
ECLASS 10.0	27-21-01-22	ECLASS 11.0	27-21-01-22
ECLASS 12.0	27-21-01-22	ECLASS 13.0	27-21-01-22

PAS CMR 0,5...2,5 A DC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Tender specification sheets

Long specification

Limit-value monitoring of DC currents up to 2.5 A with switching output

limit-value monitoring component for measuring DC currents 0.5... 2.5 A with switching output. The monitoring unit is designed so that it can be plugged onto the mounting base.

Pluggable unit on base, for mounting on TS35 DIN rail

Dimensions: L/W/H 92/15.3/ 95 mm

Screw connection / Nominal cross-section

2.5 mm²

Protection degree: IP 20

Input

0.5...2.5 A DC / Reed relay coil

Switch-on threshold < 500 mA

Switch-off threshold < 50 mA

Output

1 NO / Reed contact

Switching current max 100 mA AC/DC

Switching voltage 100 V AC / 50 V DC

Ambient temperature range 0 °C...+55 °C

Secure isolation

EN 50178,

2-way isolation up to 6 kV

Test voltage 4

kVeff / 1 min. input against output

Rated voltage

300 V AC/DC at overvoltage category III and pollution degree 2

Approvals cULus

Type

PAS CMR 0.5...2.5 A DC

Short specification

Limit-value monitoring of DC currents up to 2.5 A with switching output

limit-value monitoring component for measuring DC currents 0.5... 2.5 A with switching output. The monitoring unit is designed so that it can be plugged onto the mounting base.

PAS CMR 0,5...2,5 A DC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Downloads

Approval/Certificate/Document of Conformity	Application notes – Declaration of Conformity
User Documentation	Instruction sheet
Catalogues	Catalogues in PDF-format
Brochures	



PAS CMR 0,5...2,5 A DC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Electric symbol



PAS CMR 0,5...2,5 A DC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****PLUGSERIES****General ordering data**

Type	ZQV 2.5N 1/4-2 SW	Version
Order No.	1784270000	PLUGSERIES, Cross-connector
GTIN (EAN)	4032248214679	
Qty.	60 pc(s).	
Type	ZQV 2.5N 1/4-2 BL	Version
Order No.	1784290000	PLUGSERIES, Cross-connector
GTIN (EAN)	4032248216383	
Qty.	60 pc(s).	
Type	ZQV 2.5N 1/4-2 RT	Version
Order No.	1784280000	PLUGSERIES, Cross-connector
GTIN (EAN)	4032248214686	
Qty.	60 pc(s).	
Type	PRC HALTEBUEGEL	Version
Order No.	8536700000	PLUGSERIES, Retaining clip
GTIN (EAN)	4032248171965	
Qty.	100 pc(s).	

PAS CMR 0,5...2,5 A DC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Blank**

WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	WS 15/5 MC NE WS	Version
Order No.	1609880000	WS, Terminal marker, 15 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4008190203504	Allen-Bradley, white
Qty.	480 pc(s).	

Blank

WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	WS 10/5 MC NE WS	Version
Order No.	1635000000	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4008190261948	Allen-Bradley, white
Qty.	720 pc(s).	