

IE-FM6Z2V00003MST0ST0X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Assembled IE cables, FO patch cable, multimode, ST-ST,
orange, Core diameter 62.5 µm

General ordering data

| | |
|------------|--|
| Version | Patch cable, ST, ST IP 20, 62.5 µm, PVC, 3 m |
| Order No. | 8813290000 |
| Type | IE-FM6Z2V00003MST0ST0X |
| GTIN (EAN) | 4032248513147 |
| Qty. | 1 pc(s). |

IE-FM6Z2V00003MST0ST0X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|------|-----------------|-------------|
| Length | 3 m | Length (inches) | 118.11 inch |
| Net weight | 64 g | | |

Temperatures

| | | | |
|--------------------------|----------------|-----------------------|------------|
| Storage temperature | -25 °C...75 °C | Operating temperature | -5 °C...75 |
| Installation temperature | -5 °C...50 °C | | |

General standards

| | |
|--------------------|-------------|
| Connector standard | IEC 61754-2 |
|--------------------|-------------|

Standards

| | |
|--------------------|-------------|
| Connector standard | IEC 61754-2 |
|--------------------|-------------|

Cable structure

| | | | |
|-----------------------|----------|------------------|---------|
| Cable layout | ZIPCORD | Core diameter | 62.5 µm |
| Material sheath | PVC | Primary coating | 245 µm |
| Sheath diameter | 3*6 mm | Sheathing colour | orange |
| Standard designations | I-V(ZN)Y | | |

Mechanical and material properties of cable

| | | | |
|--------------------------------|-------|---------------------------------|-------|
| Min. bending radius, once only | 30 mm | Min. bending radius, repetitive | 60 mm |
|--------------------------------|-------|---------------------------------|-------|

Plug

| | | | |
|-----------|---|------------|---|
| Plug left | ST, IP20, male contact, straight, plug, Plastic, unshielded | Plug right | ST, IP20, male contact, straight, plug, Plastic, unshielded |
|-----------|---|------------|---|

Plug, left

| | |
|-----------|---|
| Plug left | ST, IP20, male contact, straight, plug, Plastic, unshielded |
|-----------|---|

Plug, right

| | |
|------------|---|
| Plug right | ST, IP20, male contact, straight, plug, Plastic, unshielded |
|------------|---|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002607 | ETIM 7.0 | EC002607 |
| ETIM 8.0 | EC002607 | ETIM 9.0 | EC002607 |
| ECLASS 9.0 | 27-06-10-03 | ECLASS 9.1 | 27-06-10-03 |
| ECLASS 10.0 | 27-06-10-03 | ECLASS 11.0 | 27-06-10-03 |
| ECLASS 12.0 | 27-06-10-03 | ECLASS 13.0 | 27-06-10-03 |

IE-FM6Z2V00003MST0ST0X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 67cf1078-beca-4687-860b-dc475a6ec24a |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| User Documentation | MAN IE GUIDE DE MAN IE GUIDE EN |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN |

IE-FM6Z2V00003MST0ST0X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Detailed drawing

