

WAVEFILTER 3A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Simple radio noise suppression in the cabinet thanks to WAVEFILTER**

The WAVEFILTER series eliminates the need for time-consuming bolting processes of mains filters. The filters are snapped onto TS 35 and connected to the device whose noise is to be suppressed. The two-stage, 22.5 mm wide WAVEFILTER, in 1 A, 3 A, 6 A and 10 A versions, offers high attenuation at all voltage levels from 5 V, 12 V, 24 V, 48 V, 60 V, 120 V up to 250 V.

General ordering data

Version	WAVESERIES, Surge protection, Surge protection, Attenuation at 100 MHz: 30 dB
Order No.	8614780000
Type	WAVEFILTER 3A
GTIN (EAN)	4032248277070
Qty.	1 pc(s).

WAVEFILTER 3A

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	92 mm	Depth (inches)	3.622 inch
Height	73 mm	Height (inches)	2.874 inch
Width	22.5 mm	Width (inches)	0.886 inch
Net weight	79.79 g		

Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-20 °C...40 °C
---------------------	----------------	-----------------------	----------------

General data

Colour	black	Design	Wave 22.5 L
Height with TS 35	112.4 mm	Protection degree	IP20
Rail	TS 35	Segment	Power distribution
Version	Surge protection		

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

Rated data IEC / EN

Attenuation at 0.15 MHz	< 0.5 dB	Attenuation at 1 MHz	18 dB
Attenuation at 10 MHz	45 dB	Attenuation at 100 MHz	30 dB
Capacitance	C _x / C _{and} : 33nF	Fuse	5 A
Inductance L and L1	2 mH	Leakage current at U _n	190 µA
Rated current I _N	3 A	Rated voltage (AC)	250 V
Rated voltage (DC)	250 V	Test voltage P-N	1700 V DC
Test voltage P/N-PE	2000 V AC	Voltage type	AC/DC

Connection data

Cross-section	2.5 mm ²	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	2.5 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2.5 mm ²
Wire connection cross section, finely stranded, min.	0.5 mm ²	Wire connection cross section, finely stranded, max.	2.5 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	0.5 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	1.5 mm ²

Classifications

ETIM 6.0	EC002623	ETIM 7.0	EC002623
ETIM 8.0	EC002623	ETIM 9.0	EC002623
ECLASS 9.0	27-18-28-14	ECLASS 9.1	27-42-02-08
ECLASS 10.0	27-18-28-14	ECLASS 11.0	27-18-28-14
ECLASS 12.0	27-18-28-14	ECLASS 13.0	27-18-28-14

WAVEFILTER 3A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



ROHS Conform

UL File Number Search UL Website

Certificate No. (cURus) E64388

DownloadsApproval/Certificate/Document of Conformity [EU Konformitätserklärung / EU Declaration of Conformity](#)Engineering Data [CAD data – STEP](#)User Documentation [Operating instructions](#)Catalogues [Catalogues in PDF-format](#)


Brochures

WAVEFILTER 3A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings****Electric symbol**

Circuit diagram

