

**FBCON PA CG 2WAY LIMITER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Do not use product for new  
developments



For standard industrial applications (non-hazardous areas), PROFIBUS PA junction boxes and limiters are available as 1-way, 2-way, 4-way, and 8-way distributors. FBCon limiters are designed to protect connected field devices from over voltages and short circuits. As voltage-limiting protective elements, suppressor diodes are used. Due to the integrated current limitation, the segment is also protected against short circuit on a spur line. EMC cable glands, protection class IP66 and a wide operating temperature range safely protect your connections in harsh environments.

**Functionality**

- EMC cable glands for trunk and spurs
- M12 connector for spurs
- External earthing stud
- Pressure equalizing element
- Protection class IP66
- Aluminium and stainless-steel versions
- Profibus PA / Foundation Fieldbus compatible

Note: The use of FBCon products with aluminum enclosures and / or M12 connectors is not recommended in strongly saline environments.

**General ordering data**

Version	Standard distributor with current limiting, 2-channel distributor LIMITER, IP66
Order No.	<a href="#">8714210000</a>
Type	FBCON PA CG 2WAY LIMITER
GTIN (EAN)	4032248398294
Qty.	1 pc(s).
Delivery status	<b>This article will no longer be available in the future.</b>
Available until	2024-01-14
Alternative product	<a href="#">2624390000</a>

## FBCON PA CG 2WAY LIMITER

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	36 mm	Height (inches)	1.417 inch
Width	64 mm	Width (inches)	2.52 inch
Length	98 mm	Length (inches)	3.858 inch
Net weight	352 g		

## Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...55 °C
---------------------	----------------	-----------------------	----------------

## Technical data

Bus system	Profibus-PA, Foundation Fieldbus	Cable glands	Brass cable gland
Connection type PE	Spur line with cable gland	Current limiting	adjustable, 20 mA, 40 mA, 60 mA
Design of housing	With pressure compensation element	Housing main material	Aluminium, AlSi12
Housing surface	powder coating	Operating voltage $U_{max}$ , max.	18 V DC $\pm 20\%$
Protection degree	IP66	Type of distribution	2-channel distributor LIMITER
Type of mounting	surface-mounted		

## Classifications

ETIM 6.0	EC001604	ETIM 7.0	EC001604
ETIM 8.0	EC001604	ETIM 9.0	EC001604
ECLASS 9.0	27-24-26-08	ECLASS 9.1	27-24-26-08
ECLASS 10.0	27-24-26-08	ECLASS 11.0	27-24-26-08
ECLASS 12.0	27-44-01-11	ECLASS 13.0	27-44-01-11

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	3a5f5913-76fc-4ff5-8563-4463f80bbe02

## Approvals

ROHS	Conform
------	---------

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Application notes – Certification UL</a> <a href="#">Application notes – Declaration of Conformity.pdf</a>
Software	<a href="#">Runtime Software – WI-Segment-Calculator</a>
User Documentation	<a href="#">Quick start guide – assembly instruction german / english</a> <a href="#">Quick start guide – Application-Guide-Planning and installing Fieldbus networks-us-ing-FBCon_english_deutsch</a> <a href="#">Device description – FBCon Segment Calculator_english</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## FBCON PA CG 2WAY LIMITER

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

