

**JPP PNP NPN 24VDC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The JPP level converters convert NPN signals into PNP signals and vice versa. This guarantees optimum adaptation to existing circuits.

**General ordering data**

Version	JACKPAC, Level converter, Rated control voltage: 18...24...30 V DC , Rated switching voltage: 18...30 V DC, Continuous current: 0.4 A, M12 plug/socket, A-coded
Order No.	<a href="#">8857030000</a>
Type	JPP PNP NPN 24VDC
GTIN (EAN)	4032248573332
Qty.	1 pc(s).

## JPP PNP NPN 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	14.4 mm	Height (inches)	0.567 inch
Width	36 mm	Width (inches)	1.417 inch
Length	83 mm	Length (inches)	3.268 inch
Net weight	41 g		

## Temperatures

Storage temperature	-20 °C...85 °C	Operating temperature	0 °C...60
---------------------	----------------	-----------------------	-----------

## Input

Rated control voltage	18...24...30 V DC	Rated control voltage	18...30 V DC
-----------------------	-------------------	-----------------------	--------------

## Control side

Rated control voltage	18...24...30 V DC	Sensor	2-/ 3-Conductor Sensor PNP-Type
Input current for sensor	< 200 mA		

## Output

Continuous current	Current	0.4 A
Rated switching voltage	min.	30 V
	max.	18 V
	Voltage type	DC
Rated switching voltage	18...30 V DC	
Continuous current	0.4 A	

## Load side

Rated switching voltage	18...30 V DC	Continuous current	0.4 A
Rated switching current	400 mA	Voltage drop at max. load	≤ 0.3 V

## General data

Colour	grey
--------	------

## Insulation coordination

Rated voltage	32 V	Pollution severity	2
Surge voltage category	I	Impulse withstand voltage	500 V
Protection degree	IP67		

## Further details of approvals / standards

Standards	DIN EN 50178, UL508	Certificate no. (cULus)	E141197
-----------	---------------------	-------------------------	---------

## Connection data

Wire connection method	M12 plug/socket, A-coded
------------------------	--------------------------

## output

Switching voltage, max.	18...30 V DC
-------------------------	--------------

Creation date April 27, 2024 8:12:43 PM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

## JPP PNP NPN 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Ratings IECEx/ATEX/cUL

Certificate no. (cULus) E141197

## Technical specifications for cable

Number of poles 1

## Classifications

ETIM 6.0	EC001134	ETIM 7.0	EC001134
ETIM 8.0	EC001134	ETIM 9.0	EC001134
ECLASS 9.0	19-17-92-90	ECLASS 9.1	27-21-91-90
ECLASS 10.0	19-17-92-90	ECLASS 11.0	19-17-90-90
ECLASS 12.0	19-17-90-90	ECLASS 13.0	19-17-90-90

## Environmental Product Compliance

REACH SVHC Lead 7439-92-1

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>


## JPP PNP NPN 24VDC

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Dimensioned drawing



### Pinning



## JPP PNP NPN 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## PUR halogen-free black (U)



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

## General ordering data

Type	SAIL-M12GM12G-5-0.6U	Version
Order No.	<a href="#">9457340060</a>	Sensor/actuator line, Connecting line, M12 / M12, Number of poles :
GTIN (EAN)	4008190311247	5, 0.6 m, pin, straight - socket, straight, Shielded: No, LED: No, Sheath
Qty.	1 pc(s).	material: PUR, Halogen: No
Type	SAIL-M12GM12G-5-0.3U	Version
Order No.	<a href="#">9457340030</a>	Sensor/actuator line, Connecting line, M12 / M12, Number of poles :
GTIN (EAN)	4008190311230	5, 0.3 m, pin, straight - socket, straight, Shielded: No, LED: No, Sheath
Qty.	1 pc(s).	material: PUR, Halogen: No
Type	SAIL-M12GM12G-5-1.5U	Version
Order No.	<a href="#">9457340150</a>	Sensor/actuator line, Connecting line, M12 / M12, Number of poles :
GTIN (EAN)	4008190311278	5, 1.5 m, pin, straight - socket, straight, Shielded: No, LED: No, Sheath
Qty.	1 pc(s).	material: PUR, Halogen: No

## Screwty® cable gland tool with torque function



## The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

## General ordering data

Type	SCREWTY-M12-DM	Version	Packaging
Order No.	<a href="#">1900001000</a>	Cable gland tool for moulded M12 lines	Cardboard
GTIN (EAN)	4032248436408		box
Qty.	1 pc(s).		

**JPP PNP NPN 24VDC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Distributors****General ordering data**

Type	SAI-Y-5S PARA 2M12	Version
Order No.	<a href="#">1783430000</a>	Y-plug, M12 / M12
GTIN (EAN)	4032248183364	
Qty.	1 pc(s).	

**JACKPAC® Zubehör**

Weidmüller is now one of the industry's leading international providers of connectors. An important mainstay in this product family are the circular connectors, which Weidmüller groups under the product name SAI. In the development of SAI products, Weidmüller engineers have always concentrated on achieving rational, cost-effective installation concepts, and – in cooperation with major users – have supplied the markets with well-conceived products which set standards in terms of functionality and quality across the globe. An example is the Jackpac® product family. These modules are waterproof signal converters.

**General ordering data**

Type	JP CLIP M	Version
Order No.	<a href="#">8778490000</a>	JACKPAC, Relay module
GTIN (EAN)	4032248448418	
Qty.	10 pc(s).	