

WAS1 CMA LP 1/5/10A EX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Output current loop fed AC current monitoring components WAS/WAZ1 CMA LP.

They can measure single-phase 50/60 Hz AC currents of up to 10 A using the Root Mean Square (RMS) method on the input side. They can also be switched between three ranges. No external power supply is used; the supply is only via the 4...20 mA current loop on the output side.

The input and output circuits are securely isolated with 4 kV.

The monitoring components come in a 17.5-mm-wide WAVEBOX housing. These devices can be used in many process automation applications because they are not dependent on an external power supply.

International approvals (such as ATEX Zone 2 and UL C1D2) also permit usage in explosion-risk zones.

General ordering data

Version	Current monitoring, Input current: 0...1 A AC/ 0...5 A AC/ 0...10 A AC, Output : 4-20 mA, (loop powered)
Order No.	8975590000
Type	WAS1 CMA LP 1/5/10A EX
GTIN (EAN)	4050118023640
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2023-12-30
Alternative product	2044850000

WAS1 CMA LP 1/5/10A EX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	112.4 mm	Depth (inches)	4.425 inch
Width	22.5 mm	Width (inches)	0.886 inch
Length	72 mm	Length (inches)	2.835 inch
Net weight	101 g		

Temperatures

Storage temperature	-20 °C...70 °C	Operating temperature	0 °C...70 °C
Humidity at operating temperature	0...95 % (no condensation)		

Probability of failure

SIL in compliance with IEC 61508	None
----------------------------------	------

Input

Input current	0...1 A AC/ 0...5 A AC/ 0...10 A AC	Input frequency	50...60Hz
Number of inputs	1		

Output

Load impedance current	≤ 600 Ω	Number of outputs	1
Offset current	max. 100 µA	Output current	4...20 mA (current loop)
Output signal limit	Approx. 24 mA		

Output (digital)

Max. switching voltage, AC	0 V	Rated switching current	0.1 A
Status indicator	LED ON: OK; LED flashing: signal out of range; LED OFF: Error		

Output (analogue)

Output current	4...20 mA (current loop)
----------------	--------------------------

General data

Accuracy	0.5 % FSR	Configuration	DIP switch
Galvanic isolation	2-way isolator	Rail	TS 35
Step response time	typ. 700 ms	Temperature coefficient	≤ 200 ppm/K
Voltage supply	13...30 V DC, via output current loop		

Insulation coordination

EMC standards	EN 55011, EN 61000-6	Galvanic isolation	2-way isolator
Impulse withstand voltage	6 kV	Insulation voltage	4 kV _{eff} / 5 s
Pollution severity	2	Rated voltage	300 V
Surge voltage category	III		

WAS1 CMA LP 1/5/10A EX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Connection data**

Type of connection	Screw connection	Clamping range, rated connection	2.5 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2.5 mm ²

Classifications

ETIM 6.0	EC002653	ETIM 7.0	EC002653
ETIM 8.0	EC002653	ETIM 9.0	EC002653
ECLASS 9.0	27-21-01-20	ECLASS 9.1	27-21-01-20
ECLASS 10.0	27-21-01-20	ECLASS 11.0	27-21-01-20
ECLASS 12.0	27-21-01-20	ECLASS 13.0	27-21-01-20

WAS1 CMA LP 1/5/10A EX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Tender specification sheets

Long specification

Monitoring component for AC currents up to 10A with 4...20 mA loop feed and electrical isolation
Current monitoring component in 22.5 mm width for recording 50/ 60 Hz AC currents 0...1 A / 0...5 A / 0...10 A. Input range can be selected using DIP switches.
Power is fed to the component via the 4...20 mA current loop on the output side.
The input and output circuits have 6 kV of electrical isolation.
Approved for ATEX Zone2 and UL C1 D2 applications.

Add-on housing for TS35 rail mounting
Dimensions: L/W/H 72/ 22.5/ 92.4 mm
Screw connection / Nominal cross-section 2.5 mm²
Protection degree: IP 20
Input 0...1 A / 0...5 A / 0...10 A AC switchable
50 / 60 Hz
Voltage of measuring circuit 250 V AC
Output 4...20 mA current loop
Load resistance < 600 Ohm Strom >1 kOhm / voltage
Transmission error < 0,5% v. E.
Temperature coefficient 200 ppm / K
Step response time typ. 700 ms
Auxiliary power via output-side current loop
Ambient temperature range 0 °C...+50 °C

Secure isolation EN 50178, 2-way isolation up to 6 kV

Test voltage 4 kV input against output
Rated voltage 300 V AC/DC at overvoltage category III

Short specification

Monitoring component for AC currents up to 10A with 4...20 mA loop feed and electrical isolation
Current monitoring component in 22.5 mm width for recording 50/ 60 Hz

AC currents 0...1 A / 0...5 A / 0...10 A. Input range can be selected using DIP switches. 4
Power is fed to the component via the 4... 20

WAS1 CMA LP 1/5/10A EX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	c2a21576-d875-4548-ae68-5e7f85ddf0c7

Important note

Product information	This product will soon be replaced by a new product. Please do not use with new systems. Please contact our technical support.
---------------------	---

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULusEX)	E223527

Downloads

Approval/Certificate/Document of Conformity	Application notes – Declaration of Conformity
User Documentation	Device description – Instruction sheet
Catalogues	Catalogues in PDF-format
Brochures	

WAS1 CMA LP 1/5/10A EX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Electric symbol

