


**H0,5/14 ZH OR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

**General ordering data**

|            |  |
|------------|--|
| Version    | Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, orange |
| Order No.  | <a href="#">9037200000</a>                                   |
| Type       | H0,5/14 ZH OR  |
| GTIN (EAN) | 4008190492397  |
| Qty.       | 500 pc(s).   |
| Packaging  | loose  |

## H0,5/14 ZH OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |
|------------|---------|
| Net weight | 0.095 g |
|------------|---------|

## Technical data

| Description of article | Twin wire end ferrule, or-<br>ange | Version | Twin wire-end ferrule |
|------------------------|------------------------------------|---------|-----------------------|
|------------------------|------------------------------------|---------|-----------------------|

## Wire-end ferrules

|   |             |                             |                     |
|---|-------------|-----------------------------|---------------------|
| Collar height (A)                       | 5 mm        | Collar width (B)            | 3 mm                |
| Colour code                             | Weidmueller | Conductor cross-section     | 0.5 mm <sup>2</sup> |
| Contact surface diameter (D1)           | 1.4 mm      | Contact surface length (L2) | 8 mm                |
| L1 in mm                                | 14 mm       | Metal sleeve thickness (S1) | 0.15 mm             |
| Plastic collar thickness (S2)           | 0.3 mm      | Stripping length            | 11 mm               |
| Wire connection cross section AWG, max. | AWG 20      |                             |                     |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000005    | ETIM 7.0    | EC000005    |
| ETIM 8.0    | EC000005    | ETIM 9.0    | EC000005    |
| ECLASS 9.0  | 27-40-02-01 | ECLASS 9.1  | 27-40-02-01 |
| ECLASS 10.0 | 27-40-02-01 | ECLASS 11.0 | 27-40-02-01 |
| ECLASS 12.0 | 27-40-02-01 | ECLASS 13.0 | 27-40-02-01 |

## Approvals

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate no. (cULus) | E499744    |

## Downloads

|                    |  |
|--------------------|--|
| Engineering Data   | <a href="#">CAD data – STEP</a>  |
| Engineering Data   | <a href="#">Zuken E3.S</a>   |
| User Documentation | <a href="#">Technical information - EN</a><br><a href="#">Technical information - DE</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>   |
| Brochures          |  |

**H0,5/14 ZH OR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Drawings****Drawing**