

**FRZ S 200****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

**General ordering data**

Version	Pliers
Order No.	<a href="#">9046380000</a>
Type	FRZ S 200
GTIN (EAN)	4032248357697
Qty.	1 pc(s).

## FRZ S 200

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	190 g		

## Technical data

Description of article	VDE-insulated long-nose pliers with cutter, 200 mm long
------------------------	---

## Pliers

Conductor diameter, max. (H)	1.8 mm	Conductor diameter, max. (MH)	2.8 mm
Cutter hardness	60 HRC	Protective insulation, 1000 V	Yes
Shape (telephone pliers)	straight	Total length	200 mm

## Classifications

ETIM 6.0	EC000835	ETIM 7.0	EC000835
ETIM 8.0	EC000835	ETIM 9.0	EC000835
ECLASS 11.0	21-04-38-16	ECLASS 12.0	21-04-38-16
ECLASS 13.0	21-04-38-16		

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	8ca6a82a-a032-451b-b9c3-381eae86b1bb

## Approvals

Approvals



## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Manufacturer's Declaration - Pliers</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

### FRZ S 200

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

