

SAIL-VSA-M12G-5.0U**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Weidmüller can supply valve plugs as connecting lines with M12 plugs and one end without connector. The status of the valve plug is shown by an LED. Every valve plug is fitted with a protective circuit. The Weidmüller range includes valve plugs of type A, B and C to DIN and industry standards. In the plugged condition they achieve IP 67 class of protection. The outlet direction is also a decisive factor: Weidmüller can also supply 0° versions, i.e. the cable outlet direction is located at the PE contact.

General ordering data

| | |
|------------|---|
| Version | Valve plug, Straight plug - valve plug, A |
| Order No. | 9457130000 |
| Type | SAIL-VSA-M12G-5.0U |
| GTIN (EAN) | 4008190311124 |
| Qty. | 1 pc(s). |

SAIL-VSA-M12G-5.0U**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 202 g

Technical specifications for cable

| | | | |
|-------------------------------|---------------------|----------------------------------|---------------------------|
| Acceleration | 5 m/s ² | Bending cycles | 2 Mio |
| Bending radius, min., moving | 10 x cable diameter | Bending radius, min., stationary | 5 x cable diameter |
| Cable length | 5 m | Colour coding | brown, blue, Green/yellow |
| Core cross-section | 0.5 mm ² | Halogen | No |
| Insulation | PP | Number of poles | 3 |
| Outside diameter | 4.6 mm ± 0.2 mm | Resistant to welding beads | No |
| Sheath material | PUR | Sheathing colour | black |
| Shielded | No | Speed | 200 m/s |
| Suitable for cable carriers | Yes | Temperature range, moving | -25...80 °C |
| Temperature range, stationary | -50...80 °C | Torsion resistance | 0 °/m |
| Welding spark resistance | No | | |

General technical data

| | | | |
|---|--|------------------------------|---------------------------------|
| All valve plugs are fitted with protective circuits | Zener diode | Coding | Design A (18 mm), M12 = A-coded |
| Connection thread | Miscellaneous | Contact material | CuZn |
| Contact surface | tinned | LED | Yes |
| Protection degree | IP67, when screwed in | Rated current | 4 A |
| Rated voltage | 24 V | Temperature range of housing | -25...+80 °C |
| Tightening torque | Mounting screw M3: 0.4 Nm, M12: 0.8 - 1.2 Nm | Version | Straight plug - valve plug |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001855 | ETIM 7.0 | EC001855 |
| ETIM 8.0 | EC001855 | ETIM 9.0 | EC001855 |
| ECLASS 9.0 | 27-06-03-12 | ECLASS 9.1 | 27-06-03-11 |
| ECLASS 10.0 | 27-06-03-12 | ECLASS 11.0 | 27-06-03-12 |
| ECLASS 12.0 | 27-06-03-12 | ECLASS 13.0 | 27-06-03-12 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 4060c755-8d0b-4d43-bdb3-4ffabe9d7497 |

Approvals

Approvals



ROHS Conform

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN |

Creation date May 20, 2024 2:26:01 AM CEST

Catalogue status 04.05.2024 / We reserve the right to make technical changes.


SAIL-VSA-M12G-5.0U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany


www.weidmueller.com

Drawings


Dimensioned drawing




Dimensioned drawing



Pole scheme



Pole scheme



Wiring diagram

