

KLIPPON K7 RAL7001**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

The aluminium Klippon® K enclosures are suitable for use in an extremely wide range of different areas. Various components can be installed inside the enclosures, and will benefit in particular from the high temperature resistance, the excellent IP protection and the good impact resistance.

No matter what kind of application the customer is planning, Weidmüller is able to provide a wide range of aluminium enclosures precisely fitting the customer's requirements.

Klippon® K enclosures for hazardous areas are available on request.

Our extensive product range offers the following advantages:

- Available in two surface finishes: natural and powder-coated (RAL 7001)
- With chloroprene moulded seal as standard (silicone moulded seal optionally available)
- Standardised closure system with Torx slotted screw head for 19 enclosure sizes
- Mounting holes outside of the gasket area
- High IP protection classes: IP66, IP67 and IP68 according to DIN EN 60529
- Impact resistance of up to 7 (10) Joules
- The enclosures are approved according ATEX, IECEx, cULus, and DNV GL as well as the empty enclosure standard.

- Suitable for railway applications according to EN 45545-2:2013
- Alloy is resistant to salt water
- Standardised distributor enclosures with threaded holes and a variety of terminal configurations

General ordering data

| | |
|------------|---|
| Version | Klippon K (aluminium empty enclosure), Empty enclosure, Aluminium enclosure, Height: 160 mm, Width: 350 mm, Depth: 100 mm, Material: Aluminium AlSi12, Powder-coated, textured, Silver grey |
| Order No. | 9529260000 |
| Type | KLIPPON K7 RAL7001 |
| GTIN (EAN) | 4008190918156 |
| Qty. | 1 pc(s). |

KLIPPON K7 RAL7001

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|-----------------------------|---------|----------------------------|------------|
| Depth | 100 mm | Depth (inches) | 3.937 inch |
| Height | 160 mm | Height (inches) | 6.299 inch |
| Width | 350 mm | Width (inches) | 13.78 inch |
| Mounting dimension - height | 140 mm | Mounting dimension - width | 330 mm |
| Net weight | 2,714 g | | |

Temperatures

| | |
|-----------------------|----------------|
| Operating temperature | -40 °C...80 °C |
|-----------------------|----------------|

Cable glands, left

| | | | |
|-----|---|-----|---|
| M12 | 8 | M16 | 6 |
| M20 | 3 | M25 | 2 |
| M32 | 2 | M40 | 1 |

Cable glands, right

| | | | |
|-----|---|-----|---|
| M12 | 8 | M16 | 6 |
| M20 | 3 | M25 | 2 |
| M32 | 2 | M40 | 1 |

Cable glands, top/bottom

| | | | |
|-----|----|-----|----|
| M12 | 42 | M16 | 26 |
| M20 | 17 | M25 | 10 |
| M32 | 6 | M40 | 5 |

Certificate numbers enclosure

| | | | |
|-------------------------|------------------|--|---------------------------|
| Approval conditions | cULus, RMRS, DNV | Certificate No. (DNV) | TAE00002SM |
| Certificate no. (cULus) | E197061 | Declaration of Conformatiy No. (DoC LVD) | DE_PS2410_160412_001ISS01 |

General information

| | | | |
|-----------------------------|--|---------------------------------|-------------------------------------|
| Access opening: height | 150.8 mm | Access opening: width | 340.8 mm |
| Areas of use | Process industry, Transportation, Marine engineering, Packaging industry, Harbour facilities, Machine construction | Enclosure attachment | |
| Flange plate | No | Impact resistance | Holes 6 mm 10 J version standard |
| Integral fixing | Threaded holes M5 | Lid | Yes |
| Lid attachment | M5 torx stainless steel screws with slot | Material | Aluminium AlSi12 |
| Material thickness of cover | 3 mm | Material thickness of enclosure | 4.6 mm |
| Max. payload | 5.6 kg | Note: protection class | IP68 (t=72h, h=1m) |
| Number of lid screws | 4 | Operating temperature, max. | 80 °C |
| Operating temperature, min. | -40 °C | Protection class (UL) | Type 4, Type 4X |
| Protection degree | IP66, IP67, IP68 | Seal material | Chloroprene |
| Standards | EN 45545-2:2013 | Surface finish | Powder-coated, textured |
| Torque for lid screws | 2.5 Nm | | |

KLIPPON K7 RAL7001

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

horizontal assembly

| | | | |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10 | 1x28 | WDU 16 / ZDU 16 | 1x23 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 1x55 | WDU 35 / ZDU 35 | 1x17 |
| WDU 4 / ZDU 4 | 1x46 | WDU 6 / ZDU 6 | 1x34 |

vertical assembly

| | | | |
|-----------------------------|---|---------------|---|
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | * | WDU 4 / ZDU 4 | * |
|-----------------------------|---|---------------|---|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000261 | ETIM 7.0 | EC000261 |
| ETIM 8.0 | EC000261 | ETIM 9.0 | EC000261 |
| ECLASS 9.0 | 27-18-01-01 | ECLASS 9.1 | 27-18-92-90 |
| ECLASS 10.0 | 27-18-01-01 | ECLASS 11.0 | 27-18-01-01 |
| ECLASS 12.0 | 27-18-01-01 | ECLASS 13.0 | 27-18-01-01 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 9e4cab4e-239c-4e14-b9df-a0fee300d28a |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E197061 |


Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | TAE00002SM EU Declaration of Conformity - Klippon K Empty Enclosures - DoC DE PS2410 160412 001ISS02 DoM Klippon K salt water resistance DoM Klippon K EN 45545-2 2013 Railway |
| Engineering Data | CAD data – STEP |
| Product Change Notification | Technical change to Klippon K® enclosure series Technische Änderung für Klippon® K Gehäuse 20240315-PCN-Klippon K Enclosure Instruction |
| Tender specification | Klippon K7 RAL7001_9529260000_DE Klippon K7 RAL7001_9529260000_EN |
| User Documentation | Assembly guidelines - empty enclosures |
| Catalogues | Catalogues in PDF-format |
| Brochures | MB KLIPPON ENCL.TECN EN FL RAILWAY 2014 EN FL RAILWAY 2014 EN |

KLIPPON K7 RAL7001

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings**Dimensioned drawing**

KLIPPON K7 RAL7001

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Depth 7.5 mm



The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS 15
- Mounting plates
- Hinges
- Wall-mounted holder

General ordering data

| | | |
|------------|----------------------------|---|
| Type | TS35/324 KLIPPON K7 CSS | Version |
| Order No. | 1910130000 | Rail, TS 35, TS 35 x 7.5, Width: 324 mm, without slot, Steel, |
| GTIN (EAN) | 4032248537044 | galvanized, chromium-plated |
| Qty. | 1 pc(s). | |
| Type | TS35X7.5 ST K7 | Version |
| Order No. | 8000003905 | Rail, TS 35, TS 35 x 7.5, Width: 324 mm, without slot, Steel, |
| GTIN (EAN) | 4050118652680 | galvanized, chromium-plated |
| Qty. | 20 pc(s). | |

Klippon® K - Mounting plates



The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS 15
- Mounting plates
- Hinges
- Wall-mounted holder

General ordering data

| | | |
|------------|----------------------------|--|
| Type | MOPL K7 STAHL | Version |
| Order No. | 3073130000 | Klippon K (aluminium empty enclosure), Mounting plate, Mounting |
| GTIN (EAN) | 4008190858063 | plate, Height: 144 mm, Width: 334 mm, Depth: 2 mm, Material: Sheet |
| Qty. | 1 pc(s). | steel, galvanized, galvanized, silver |

KLIPPON K7 RAL7001

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Klippon® K - Wall-mounted holder



The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS15
- Mounting plates
- Hinges
- Wall-mounted holder

General ordering data

| | | |
|------------|----------------------------|--|
| Type | KLIPPON K MF KIT 16 | Version |
| Order No. | 9529080000 | Klippon K (aluminium empty enclosure), Mounting foot, Fixing lugs, |
| GTIN (EAN) | 4008190916299 | Height: 70 mm, Width: 33.5 mm, Depth: 12 mm, Material: Stainless |
| Qty. | 1 pc(s). | steel 1.4301, silver |

Spacer



Stainless steel spacers in three lengths to increase the distance between the mounting rails or DIN rails and the rear wall of the enclosure.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SP M6 15 MSZN | Version |
| Order No. | 3896100000 | Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm, |
| GTIN (EAN) | 4008190857851 | Depth: 15 mm, Material: Steel, silver |
| Qty. | 2 pc(s). | |
| Type | SP M6 30 MSZN | Version |
| Order No. | 3896300000 | Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm, |
| GTIN (EAN) | 4008190850241 | Depth: 30 mm, Material: Steel, silver |
| Qty. | 2 pc(s). | |
| Type | SP M6 20 MSZN | Version |
| Order No. | 3896200000 | Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm, |
| GTIN (EAN) | 4008190850234 | Depth: 20 mm, Material: Steel, silver |
| Qty. | 2 pc(s). | |

KLIPPON K7 RAL7001**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Screws**

Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | FKSC M5X8 D9/SW2.5 | Version |
| Order No. | 0295900000 | SAK Series, Allen hex screw, Screws, Number of poles: 1 |
| GTIN (EAN) | 4008190133337 | |
| Qty. | 50 pc(s). | |

Klippon® K - Hinge

The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS 15
- Mounting plates
- Hinges
- Wall-mounted holder

General ordering data

| | | |
|------------|----------------------------|---|
| Type | HG K+POK | Version |
| Order No. | 1580360000 | Klippon POK (polyester empty enclosure), External joint, Hinge, |
| GTIN (EAN) | 4008190203542 | Material: Aluminium AlSi12, silver |
| Qty. | 1 pc(s). | |

KLIPPON K7 RAL7001

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Depth 15 mm



The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS 15
- Mounting plates
- Hinges
- Wall-mounted holder

General ordering data

| | | |
|------------|----------------------------|---|
| Type | TS35X15 ST K7 | Version |
| Order No. | 8000073098 | Rail, TS 35, TS 35 x 15, Width: 324 mm, with slot, Steel, galvanic zinc |
| GTIN (EAN) | 4064675340522 | plated and passivated |
| Qty. | 20 pc(s). | |