


MP FPC 20/20**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Mounting plates, 1.5 mm sheet steel, galvanised

General ordering data

Version	FPC (polycarbonate empty enclosure), Mounting plate, Mounting plate, Height: 150 mm, Width: 185 mm, Depth: 2 mm, Material: Sheet steel, galvanized, silver
Order No.	9535920000
Type	MP FPC 20/20
GTIN (EAN)	4032248009640
Qty.	1 pc(s).

MP FPC 20/20**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	2 mm	Depth (inches)	0.079 inch
Height	150 mm	Height (inches)	5.905 inch
Width	185 mm	Width (inches)	7.283 inch
Net weight	288 g		

General information

Material	Sheet steel	Surface finish	galvanized
Type of fixing	when screwed in		

Classifications

ETIM 6.0	EC000213	ETIM 7.0	EC000213
ETIM 8.0	EC000213	ETIM 9.0	EC000213
ECLASS 9.0	27-40-06-39	ECLASS 9.1	27-18-92-90
ECLASS 10.0	27-40-06-39	ECLASS 11.0	27-40-06-39
ECLASS 12.0	27-40-06-39	ECLASS 13.0	27-40-06-39

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

MP FPC 20/20**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****TS 35**

Accessories

**General ordering data**

Type	TS35X7.5 ST FPC 20 HOR	Version
Order No.	8000037557	Rail, TS 35, TS 35 x 7.5, Width: 165 mm, with slot, without slot, Steel,
GTIN (EAN)	4050118653212	galvanized, chromium-plated
Qty.	20 pc(s).	
Type	TS35X7.5 ST FPC 20 VER	Version
Order No.	8000037558	Rail, TS 35, TS 35 x 7.5, Width: 165 mm, with slot, without slot, Steel,
GTIN (EAN)	4050118653229	galvanized, chromium-plated
Qty.	20 pc(s).	

TS 15

Accessories

**General ordering data**

Type	TS15X5 ST FPC 20 VER	Version
Order No.	8000037604	Rail, TS 15, Width: 235 mm, without slot, Steel, galvanized, chromium-
GTIN (EAN)	4050118653168	plated
Qty.	20 pc(s).	